

# Ansell

## POWERED TO PROTECT

### FLEET SERVICE

Ansell's diverse range of gloves come powered with all the right levels of cut, abrasion and chemical protection. Technicians can work on engines, tools and other machinery comfortably and confidently knowing that they're fully protected.

Reinforced gusset between thumb and index finger

#### HyFlex® 11-939R High-Tech Mechanic Glove



- Lined with Dyneema® Diamond Technology providing cut & abrasion resistance
- Fully-coated for oil repellency
- Silicone & latex-free

#### HyFlex® 11-727R Medium-Duty Mechanic Glove



- Enables wet, dry and light oil grip with dirt-masking palm coating
- Offers excellent abrasion resistance and durability
- Provides dexterity for small parts and precision handling

#### ActivArm® 97-125R High-Impact Mechanic Glove




- Delivers up to 6x more cut protection than leather
- Certified impact glove for supreme protection
- Double dipped nitrile coating provides excellent grip
- HPPE liner to keep your hands cool & comfortable all day

#### ActivArm® 97-003 Heavy-Duty Mechanic Glove



- Provides cut protection & heat resistance with DuPont™ Kevlar® yarns
- Reduces impacts and vibrations
- Enables advanced grip in wet or dry conditions





The MICROFLEX® single use gloves are created to provide great protection and comfort when working with oils and other chemicals. The thickness, texture and design of these gloves ensure durability and grip for all day efficiency.



### **MICROFLEX® SAFEGRIP™ SG-375**

**Thick, Durable Exam Glove  
with Extended Cuff**

- Three times thicker than standard latex gloves to prevent rips, snags and tears
- Textured fingertips provide secure grip
- Made with premium latex which provide comfort with a soft, elastic fit and feel



### **MICROFLEX® DURA FLOCK™ DFK-608**

**Flock Lined Disposable  
Nitrile Glove**


- Soft flock lining absorbs moisture & keeps you dry
- Thicker design to resist punctures & tears
- Extended cuff for added protection



### **MICROFLEX® Mega Texture 93-283**

**Raised Grip Disposable  
Nitrile Glove**

- Features a Mega Texture surface for secure grip
- Extended cuff provides extra protection over wrist and forearm
- The robust 0.20mm / 8mil thickness resists tearing, for better protection



### **MICROFLEX® Diamond Grip™ MF-300**

**Powder-Free Disposable  
Latex Glove**

- Thick and durable latex designed to prevent rips & tears
- Double chlorinated for easy donning and a comfortable feel
- Textured fingers for great grip



### **MICROFLEX® MidKnight™ XTRA 93-862**

**Extended Cuff Disposable  
Nitrile Glove**

- Extended cuff provides extra protection over wrist and forearm
- Robust nitrile resists a range of chemicals, oils and solvents
- Fully textured for a reliable, consistent grip



### **MICROFLEX® MidKnight™ MK-296**

**Distinct Black Disposable  
Nitrile Glove**

- Black color offers tough protection while masking dirt, oils and grease so wearers' hands look neat and professional during work
- Fully textured, for optimal grip
- Comfort, durability and consistency

For more information or a free sample call 877-750-6110  
[www.ansell.com/autoaftermarket](http://www.ansell.com/autoaftermarket)

Ansell, ® and ™ are trademarks owned by Ansell Limited or one of its affiliates. © 2020 All Rights Reserved.

**MICROFLEX® HyFlex® ACTIVARM®**