














## INDUSTRIAL PPE FOR ELECTRIC VEHICLE MANUFACTURING

Workers in Electric Vehicle (EV) manufacturing environments are exposed to a wide array of workplace hazards from electric shock to handling sharp or abrasive materials. Our products are engineered to deliver the optimum balance of performance and protection to create a more productive and safe day at work.

TYPE OF PROTECTION <i>Click the product to explore how Ansell gloves provide optimum protection in EV manufacturing.</i>		APPLICATION			
		Manufactures and Supply Cylindrical Lithium-ion Cells	Module Manufacturing	Assembly Facility	Re-Manufacturing Facility
HyFlex® 11-561 	Cut Protection	●	●	●	●
HyFlex® 11-819 ESD 	Touchscreen/ ESD Protection		●	●	
HyFlex® 11-840 	Abrasion Protection	●	●	●	●
TouchNTuff® 92-600 	Single-Use Protection	●	●	●	●
MICROFLEX® 93-243 		●	●	●	●
MICROFLEX® 93-260 		●	●	●	●
ActivArmr® Electrical Glove Class 00 - RIG0014B 	Electrical Protection	●	●	●	●
AlphaTec® 1500/1800 Standard 	Chemical Protection	●		●	
AlphaTec® 2000 Standard 		●		●	
AlphaTec® 2300 PLUS Stitched & Taped 		●		●	
AlphaTec® 4000 Ultrasonically Welded & Taped 		●		●	

For additional information, contact your local Ansell Territory Manager or visit us at [www.ansell.com](http://www.ansell.com)