

# AlphaTec® 85-301 85-303 85-305



Chemical & Liquid Protection



Chlorosulfonated polyethylene (CSM)



Heavy



## IDEAL APPLICATIONS

- Pharmaceuticals

## PRIMARY INDUSTRIES



## STANDARDS AND CERTIFICATIONS

EN388:200 3	EN374:200 3	EN374:200 3	EN388:201 6	EN ISO 374- 1:2016 Type B	EN ISO 374-5:2016
4101		AKL	3101A	AMP	VIRUS

CATEGORY III

## EXTRA FEATURES

## INCREASED COMFORT AND PROTECTION IN CRITICAL ENVIRONMENTS

### DESCRIPTION

CSM HEAVY WEIGHT ISOLATOR BOX GLOVE

- Designed for high resistance against concentrated acids and bases
- Soft, flexible material designed for ease of use
- Resists ageing from exposure to oxygen, UV rays and ozone
- Withstands temperatures up to 120°C
- White coloring for easy detection of contamination
- Increased thickness (0.6 mm) for added durability
- Available port sizes fit most isolator glove boxes

### PRODUCT DETAILS

Coating material	Chlorosulfonated Polyethylene
Grip design	Smooth
Colour	Offwhite
AQL	1.5
EN Sizes	9.5,11
Length (mm)	85-301: 800 (Port Size 203mm) 85-303: 800 (Port Size 250mm) 85-305: 800 (Port Size 300mm)
Packaging	10 pairs in black sealed bags per shipper carton

Print date 05-12-2019

Ansell Healthcare Europe N.V. (European Head Office)

Riverside Business Park, Block J

Boulevard International 55, 1070 Brussels, Belgium

Tel. +32 (0) 2 528 74 00 • Fax +32 (0) 2 528 74 01 • Fax Customer Service +32 (0) 2 528 74 03

<http://www.ansell.eu> • E-mail [info@ansell.eu](mailto:info@ansell.eu)

