




Product name	AlphaTec® 2000 STANDARD
Product material	Microporous polyethylene laminate non woven
Colours available	White, Green
Material weight	63gsm

Physical Properties - EN 14325:2004					
Test Method		Result (White fabric)	EN Class (white fabric)	Result (Green fabric)	EN Class (Green fabric)
Abrasion	EN 530	>100 Cycles	2 of 6	>10 Cycles	1 of 6
Flex cracking	EN ISO 7854	>40,000 Cycles	5 of 6	>100,000 Cycles	6 of 6
Tear resistance (MD)	EN ISO 9073-4	>20 N	2 of 6	>40 N	2 of 6
Tear resistance (CD)		>60 N		>20 N	
Tensile strength (MD)	EN ISO 13934-1	>100 N	1 of 6	>100 N	1 of 6
Tensile strength (CD)		>30 N		>30 N	
Puncture resistance	EN 863	>5 N	1 of 6	>5 N	1 of 6
Seam Strength	EN ISO 13935-2	>75 N	3 of 6	>75 N	3 of 6

Fabric Repellence & Penetration to Liquid Chemicals - EN 14325:2004					
Fabric Repellence of Liquids					
Test Chemical	Test Method	Result % (white fabric)	EN Class	Result % (green fabric)	EN Class
Sulphuric Acid (30% w/w)	EN ISO 6530	>95	3 of 3	>95	3 of 3
Sodium Hydroxide (10% w/w)		>95	3 of 3	>95	3 of 3
o-Xylene		>90	2 of 3	>90	2 of 3
Butan-1-ol		>95	3 of 3	>95	3 of 3
Fabric Penetration Resistance of Liquids					
Sulphuric Acid (30% w/w)	EN ISO 6530	<1	3 of 3	<1	3 of 3
Sodium Hydroxide (10% w/w)		<1	3 of 3	<1	3 of 3
o-Xylene		<1	3 of 3	<1	3 of 3
Butan-1-ol		<1	3 of 3	<1	3 of 3

Additional Testing					
Test Method		Result (White fabric)	EN Class (white fabric)	Result (Green fabric)	EN Class (Green fabric)
Anti-static Properties (EN 1149-5)	EN 1149-3 (Charge Decay)	$t_{50} < 4$ s	Pass	$t_{50} < 4$ s	Pass
Hydrostatic Head (Water Pressure Test)	ISO 811	>200 cm H ₂ O		>200 cm H ₂ O	

Comfort Testing			
Test Method		Result (White fabric)	Units
Air Permeability: Gurley Method	ISO 5636-5	321	s 100 cm ²
Water Vapour Resistance (R_{et})	EN 31092/ISO 11092	17.1	m ² ·Pa/W
Thermal Resistance (R_{ct})	EN 31092/ISO 11092	0.014	m ² ·K/W
Water Vapour Permeability Index (WVPI)		0.047	-
Clothing Insulation (clo) value		0.087	-

Barrier to Infective Agents - EN 14126:2003			
Test Method		Result	EN Class
Resistance to penetration by synthetic blood	ISO 16603	Pass (20 kPa)	n/a
Resistance to penetration by blood borne pathogens	ISO 16604	Pass (20 kPa)	6 of 6
Resistance to wet bacterial penetration (mechanical contact)	EN ISO 22610	No penetration (up to 75 min)	6 of 6
Resistance to biologically contaminated aerosols	ISO/DIS 22611	No penetration	3 of 3
Resistance to dry microbial penetration	ISO 22612	No penetration	3 of 3

Whole Suit Testing	
Test Method	
EN ISO 13982-1:2004+A1:2010	Type 5 : Particle Test
EN 13034:2005+A1:2009	Type 6 : Reduced Spray Test
EN 1073-2:2002	Radioactive Particulates (Class 2 of 6)*

* Coverall tested to EN 1073-2 for barrier to radioactive particles, with the exception of Clause 4.2: Puncture resistance achieves Class 1 versus the requirement of Class 2. Resistance to ignition is not tested as product already carries flammability warning. Note: Does not protect against ionizing radiation.

Safety Note: All chemical tests and breakthrough times given relate to laboratory tests on fabrics only. Seams and closures may have lower breakthrough times, particularly when worn or damaged. It is the user's responsibility to select an appropriate garment, gloves, boots and other equipment for the particular use. The user shall be responsible for determining how long the garment can be worn for the particular use and whether it can be suitably cleaned for re-use. Ansell Limited does not give any warranties or make any representations about its garments other than those contained in the official literature supplied by Ansell Limited with each garment. Ansell 2023. All rights Reserved.