

### PRODUCT INFORMATION

VIKING™ INTEGRATED RUBBER SOLES	
<b>Key Features &amp; Benefits</b>	<ul style="list-style-type: none"> <li>• Non-slip surface for grip</li> <li>• Fin-strap retainer fitted to the heel</li> </ul>
<b>Description</b>	<p>An extension of the leg, with a heavy-duty flexible rubber sole stitched and taped to the end.</p> <ul style="list-style-type: none"> <li>• Fitted as standard on VIKING™ PRO and HD</li> <li>• Fitted as an option on VIKING™ PROTECH II</li> <li>• Also available as separate spare part</li> </ul>
<b>Product Material</b>	Vulcanised rubber
<b>Colour</b>	Black
<b>Available Sizes</b>	41/42, 43/44, 45/46
VIKING™ NEOPRENE BOOTS	
<b>Key Features &amp; Benefits</b>	<ul style="list-style-type: none"> <li>• Flexible, warm and comfortable</li> <li>• Good grip</li> <li>• Fin-strap retainer fitted to the heel</li> </ul>
<b>Description</b>	<p>Made from neoprene material which is coated with rubber for added protection, and to create a waterproof product.</p> <ul style="list-style-type: none"> <li>• Fitted as standard on VIKING™ PROTECH II, HAZTECH, VTS, WRS-D and WRS</li> <li>• Fitted as an option on VIKING™ PRO and HD</li> <li>• Also available as separate spare part</li> </ul>
<b>Product Material</b>	Neoprene coated with rubber
<b>Thickness</b>	5 mm
<b>Colour</b>	Black
<b>Available Sizes</b>	36, 37, 38, 39, 40/41, 42, 43, 44, 45/46, 47, 48, 49
NITRILE RUBBER SAFETY BOOTS	
<b>Key Features &amp; Benefits</b>	<ul style="list-style-type: none"> <li>• Seamless construction for completely watertight boots</li> <li>• Provides maximum protection in contaminated waters</li> <li>• Oil and slip resistant outsole</li> </ul>
<b>Description</b>	<p>Safety boots with composite toe cap and anti-perforation mid-sole for protection against falling objects, or sharp objects.</p> <p>Fitted as an option on VIKING™ PRO, PROTECH II, HD, DIVERS DRESS, HAZTECH, VTS, WRS-D and WRS. Also available as separate spare part.</p>
<b>Product Material</b>	Nitrile/Chloroprene rubber
<b>Height</b>	390 mm
<b>Weight</b>	1.9 kg/pair
<b>Colour</b>	Black
<b>Available Sizes</b>	39, 40/41, 42, 43, 44, 45, 46/47, 48, 49/50
VIKING™ LATEX SOCKS	
<b>Key Features &amp; Benefits</b>	<ul style="list-style-type: none"> <li>• Lightweight, stretchy and flexible</li> <li>• For use with overboots</li> </ul>
<b>Description</b>	<p>Latex rubber construction similar to latex neck &amp; wrist seals. For use in conjunction with some kind of rock boot or safety overboot.</p> <p>Fitted as an option on VIKING™ HAZTECH, VTS, WRS-D and WRS. Also available as separate spare part.</p>
<b>Product Material</b>	Rubber latex
<b>Colour</b>	Black
<b>Available Sizes</b>	M/37-42, L/43-45, XL/46-48



## PRODUCT INFORMATION

VIKING™ COMMERCIAL/HARBOUR OVERBOOTS	
<b>Key Features &amp; Benefits</b>	<ul style="list-style-type: none"> <li>Protects the diver's feet from sharp objects on the sea bed</li> <li>Intended for heavy duty use</li> </ul>
<b>Description</b>	Made to be worn over rubber dry suits to protect the diver's feet from sharp objects on the sea bed. They also offer protection to the suit itself.
<b>Product Material</b>	1.6 mm textile reinforced rubber with a 2.5 mm reinforced rubber toe cap
<b>Colour</b>	Black/Red
<b>Available Sizes</b>	M, L
VIKING™ LEAD INSOLES (FOR USE WITH COMMERCIAL/HARBOUR OVERBOOTS)	
<b>Key Features &amp; Benefits</b>	<ul style="list-style-type: none"> <li>Adds diver stability in moving water</li> <li>Available in 2 different sizes &amp; weights</li> </ul>
<b>Description</b>	Intended for use with VIKING™ Commercial/Harbour Overboots, to add stability to the diver when working in moving water.
<b>Product Material</b>	Plastic coated lead
<b>Length</b>	29 cm (size M); 32 cm (size L)
<b>Weight</b>	5.7 kg/pair (size M); 6.0 kg/pair (size L)
<b>Colour</b>	Black (size M); Yellow (size L)
<b>Available Sizes</b>	M (for size M boots); L (for size L boots)
VIKING™ NEOPRENE BOOTS (FOR USE WITH HOT WATER SUIT)	
<b>Key Features &amp; Benefits</b>	<ul style="list-style-type: none"> <li>Moulded rubber outsoles for good grip and protection</li> <li>Hook and loop fasteners for attachment to VIKING™ Hot Water Suit</li> </ul>
<b>Description</b>	Designed for use with VIKING™ Hot Water Suit (HWS). Fitted with hook and loop fasteners for attachment to the suit.
<b>Product Material</b>	Neoprene
<b>Thickness</b>	5 mm
<b>Colour</b>	Black
<b>Available Sizes</b>	M/43, L/44, XL/45-46



### For additional information, visit us at [ansell.com](https://www.ansell.com) or contact us at:

#### Europe, Middle East & Africa Region

Ansell Protective Solutions AB  
T: +46 10 205 1800  
order.protective@ansell.com

#### Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.  
T: +52 442 248 1544 / 248 3133

#### Australia

Ansell Limited  
T: +61 1800 337 041

#### North America Region

Ansell Healthcare LLC  
T: +1 800 800 0444  
info@ansell.com

#### Asia Pacific Region

Ansell Protective Solutions  
T: +603 8310 6688  
order.protective@ansell.com