

ACTIVARMR™

Electrical Protection Class 2 - RIG214Y

Ergonomically designed natural rubber insulating gloves for all-day safety and comfort

Previously known as: E018Y



Electrical



Medium Duty

High-voltage electrical safety gloves, ensuring flexible, durable hand protection*

- **Heightened durability and flexibility:** ActivArmTM Electrical Protection Class 2 - RIG214Y gloves are made from tough, flexible natural latex, using an environmentally friendly dipping process
- **Advanced ergonomics:** Their ergonomic hand-at-rest shape and non-splayed fingers reduce hand fatigue
- **Elevated comfort:** A flared cuff leaves ample room for clothing and ventilation
- **Increased practicality:** These electrical protection gloves boast a smooth finish, for easy donning and doffing
- **Certified protection:** They meet relevant NFPA, OSHA and CSA standards, possess EN Category R certification*, are arc flash certified (APC 2 in combination with 96-003 leather gloves)**, and meet Category C cold resistance standards
- **Specialized defenses:** These electrical safety gloves can withstand a touch voltage AC maximum of 17000 V (DC maximum 25500)
*for passing A+Z+H properties (as required by EN standards)
**ATPV : 14 cal/cm², EBT : 33 cal/cm² with 96-003 leather gloves



Industries

- Automotive
- Construction
- Energy

Applications

- Applications with risk of touch voltage
- Electrical Contractors
- Hybrid engine manufacturing and repair
- Maintenance Repairs and Operations in all industrial environments (MRO)
- Mass Transit Repair and Maintenance
- Power maintenance, repair & transmission
- Telecom repair near electrical wires

ACTIVARMR™

Electrical Protection Class 2 - RIG214Y


Ergonomically designed natural rubber insulating gloves for all-day safety and comfort

Previously known as: E018Y

Key Features

- ♦ **Natural rubber latex formulation:** Excellent flexibility and durability
 - ♦ **Ergonomic design:** Better dexterity and comfort, reduced hand fatigue
 - ♦ **Generous flared cuff:** Ample room for clothing and improved ventilation
- *Arc flash certified as per IEC 614821-2:2014 and ASTM F2675:2021 standards

Performance Standards & Regulatory Compliance



Specifications

BRAND STYLE	DESCRIPTION	SIZE	LENGTH	COATING COLOR	PACKAGE
ActivArmrr Electrical Protection Class 2 - RIG214Y	Coating Material: Natural Rubber Latex Cuff Style: Straight Cuff with rolled beaded edge	8, 9, 10, 11, 12	360 / 14.17	Yellow	• 1 pair/pack, 10 pairs/carton

For additional information visit us at www.ansell.com, or call us at

Europe, Middle East & Africa Region

Ansell Healthcare Europe NV
Riverside Business Park
Blvd International, 55
1070 Brussels, Belgium
T: +32 (0) 2 528 74 00
F: +32 (0) 2 528 74 01

Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.
Blvd. Bernardo Quintana No. 7001-C,
Q7001 Torre II,
Suites 1304, 1305 y 1306,
Col. Centro Sur, c.p. 76079
Queretaro, Qro. Mexico
T: +52 442 248 1544 / 248 3133

North America Region

Ansell Healthcare Products LLC
111 Wood Avenue South,
Suite 900
Iselin, NJ 08830, USA
T: +1 800 800 0444
F: +1 800 800 0445

Canada

Ansell Canada
105 Lauder
Cowansville, QC J2K 2K8
Canada
T: +1 800 363 8340
F: +1 800 267 3551

Australia

Ansell Limited
Level 3, 678 Victoria Street,
Richmond, Vic, 3121
Australia
T: +61 1800 337 041
F: +61 1800 803 578

Asia Pacific Region

Ansell Global Trading Center
(Malaysia) Sdn Bhd
Prima 6, Prima Avenue
Block 3512, Jalan Teknokrat 6
T: +603 8310 6688
F: +603 8310 6699

Ansell, ® and ™ are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending: www.ansell.com/patentmarking © 2025 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.

