


# SYNSATION™ PF

Vinyl, powder-free examination glove dual-marked for a wide range of applications (only available in EMEA)

## Vinyl, powder-free exam gloves dual-marked for a wide range of applications

- **Cost-effective:** These vinyl gloves are a cost-effective alternative to latex
- **Medical-grade protection:** These gloves are CE marked as both Class I medical device and Category III personal protective equipment so are suitable for both medical and industrial applications
- **Easy donning:** A coated inner surface provides a comfortable feel while making donning easier
- **Beaded cuff:** The beaded cuff design prevents roll down during work
- **Reduced allergy risk:** Vinyl material prevents Type I (latex) allergic reactions



### Industries

- Healthcare

### Recommended For

- Brief, low-risk examination procedures
- Protection from Type I latex allergy in HCW's or patients


# TECHNICAL DATA SHEET

Product Information	
<b>Material</b>	Vinyl (Polyvinyl Chloride)
<b>External Glove Surface</b>	Smooth
<b>Audit Standards</b>	ISO 13485, ISO 9001
<b>Product Certification</b>	Medical Device Regulation (EU) 2017/745 Class I, Personal Protective Equipment Regulation (EU) 2016/425 Category III risks, CE 0493, Category III, EN 16523-1, EN ISO 374-1:2016 Type C, EN ISO 374-5:2016 Virus, EN 455 1-4, EN ISO 21420:2020, ISO 13485, ISO 9001, ISO 10993-10:2002, UKCA
<b>Packaging Overview</b>	100 gloves per dispenser 10 dispensers per case 1000 gloves per case
<b>Storage Instructions</b>	Keep out of direct sunlight; store in a cool and dry place. Keep away from sources of ozone or ignition.
<b>Country Of Origin</b>	China
<b>Antistatic</b>	Not Tested

## PHYSICAL PROPERTIES

	Typical Values		Testing Method
Length (mm/inches)	240 / 9.5		ASTM D3767, EN 420
Freedom from Holes (Inspection level I)	1.5 AQL		ASTM D5151, EN 455-1
Palm Thickness (mm/mils)	0.11 / 4.3		ASTM D3767, EN 420
Finger Thickness (mm/mils)	0.10 / 3.9		ASTM D3767, EN 420
	<b>BEFORE AGING</b>	<b>AFTER AGING</b>	
Ultimate Tensile Strength (MPa)	≥11	≥11	ASTM D412 & D573
Elongation at Break (%)	≥300	≥300	ASTM D412
Force at break (N)	≥3.6	≥3.6	

## Performance Standards and Regulatory Compliance



For additional information visit us at [www.ansell.com](http://www.ansell.com), or call us at

**Europe, Middle East & Africa Region**  
Ansell Healthcare Europe NV  
T: +32 (0) 2 528 74 00  
F: +32 (0) 2 528 74 01

**Asia Pacific Region**  
MY +603 8310 6688  
apac.medical@ansell.com  
CN: +86 21 38275000  
infochina@ansell.com  
JP: +813 5549 8151  
info.medical.jp@ansell.com

**North America Region**  
Ansell Healthcare Products LLC  
T: +1 800 800 0444  
F: +1 800 800 0445

**Latin America & Caribbean Region**  
BR +55 (11) 3356-3100  
latam.medical@ansell.com  
MX: +52 442 296 2050  
latam.medical@ansell.com  
CO: +57 1 288 3247  
latam.medical@ansell.com

**Australia**  
Ansell Limited  
T: +61 1800 337 041  
F: +61 1800 803 578

**Russia**  
Ansell PYC  
Ten. +7 495 258 13 16

Technology



Ansell, ® and ™ are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending; [www.ansell.com/patentmarking](http://www.ansell.com/patentmarking) © 2025 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.

