



BioClean™ Clearview Autoclavable Goggles BCAH

Silicone clearview autoclavable goggles with anti-scratch and anti-fog properties

- **Elevated comfort:** These BioClean™ clearview goggles feature a non-linting, latex-free headband with a super-soft lightweight silicone rubber frame that enables prolonged use and user comfort
- **Advanced defenses:** BioClean™ Clearview Autoclavable Goggles BCAH possess an indirect ventilation system that helps reduce the risk of contamination entering the controlled environment
- **Maximized view:** These BioClean™ clearview goggles provide wearers an optically correct, toughened polycarbonate anti-scratch and anti-fog lens, making them ideal for use over eyeglasses
- **Improved durability:** These autoclavable cleanroom goggles can tolerate up to 1 gamma irradiation cycles and are tested to withstand >40 autoclave cycles of 30 minutes duration at 121°C/250°F. Anti-fog performance remaining for up to 25 cycles with no signs of degradation (under laboratory conditions)



Key Features and Benefits

- **Lightweight material:** Enables prolonged use and user comfort
- **Indirect ventilation system:** Lowers the risk of contamination
- **Anti-scratch, anti-fog properties:** For unobstructed vision

Industries

- Controlled and Critical Environments
- Laboratory and Research
- Production and Manufacturing

Recommended For

- Medical Device Manufacturing
- Biotechnologies Blending operations
- Handling active material
- Maintaining equipment and instruments
- Organic and material synthesis
- Preparing pharmaceutical products

WWW.ANSELL.COM



- Clean room cleaning and preparing
- Nutraceutical manufacturing



BioClean™ Clearview Autoclavable Goggles BCAH

TECHNICAL DATA SHEET

PRODUCT INFORMATION

Material	Polycarbonate, Silicone rubber, Polypropylene
Color	White
Audit Standards	Manufacturing QMS Audit Standards ISO 9001
Packaging Overview	<p>Goggle (BCAH): One piece per sealed PE bag (to be removed prior to autoclaving); 12 bags per inner box; five boxes per carton (60 pieces)</p> <p>Replacement Lens (BCAH-SL): One piece per sealed PE bag; 10 bags per inner box; 10 boxes per carton (100 pieces)</p> <p>Replacement Strap (BCAH-SS): 25 pieces per sealed PE bag; two bags per inner box; 10 boxes per carton (500 pieces)</p> <p>Accessory Set (BCAH-ACC1): One set of accessories per bag; 100 sets per outer bag; 100-300 sets per carton.</p>
Country Of Origin	Malaysia
Sterilization Method	Supplied non-sterile. To be autoclaved at 121°C/250°F for 30 minutes.
Cleanroom Class	Class 10/ISO 4 & EU GMP Grade A
Shelf Life	Five (5) years from date of manufacture.
Storage Instructions	Store in a dry, cool place (<40°C) away from direct sunlight and fluorescent light.
Weight	106g

PHYSICAL PROPERTIES

Overall Dimensions	<p>Total Weight (± 2g) 106g</p> <p>Lens Thickness (± 0.3mm) 1mm</p> <p>Bridge Width (± 0.5mm) 50mm</p> <p>Bridge Height(±0.5mm)20mm</p> <p>Overall Width (hinge to hinge)(±3mm) 180mm Overall Height (± 3mm) 92mm</p>
---------------------------	-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------

ORDERING INFORMATION

	SIZE	Autoclavable Goggles
BCAH	REORDER NO.	BCAH



BioClean™ Clearview Autoclavable Goggles BCAH

EXPLANATION OF FRAME MARKINGS

Required Markings	Markings On Frame	Meaning
Manufacturers Identification Mark	BioClean™	BioClean™

For additional information visit us at www.ansell.com, or call us at

Europe, Middle East & Africa Region

Ansell Healthcare Europe NV
T: +32 (0) 2 528 74 00
F: +32 (0) 2 528 74 01

Asia Pacific Region

Ansell Global Trading Center
T: +603 8310 6688
F: +603 8310 6699

North America Region

Ansell Healthcare Products LLC
US T: +1 800 800 0444
US F: +1 800 800 0445
CA T: +1-800-363-8340

Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.
T: +52 442 248 1544 / 248 3133

Australia

Ansell Limited
T: +61 1800 337 041
F: +61 1800 803 578

UK

Ansell Nitritex
T: +44 1638 663338
F: +44 1638 668890

Ansell, ® and ™ are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending.
www.ansell.com/patentmarking © 2024 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.



