

## High-visibility orange nitrile exam gloves, for protection that you can see

- **High visibility:** MICROFLEX™ 93-856 are robust, high visibility orange nitrile medical exam gloves that protect hands in demanding environments — their high-visibility orange color makes them easy to see in emergency situations
- **Secure grip:** These gloves work exceptionally well in oily environments — with their textured fingers, wearers can confidently grip tools and materials in every situation
- **Added protection:** These orange nitrile gloves also feature an extended cuff for added protection of the wrist and forearm, and offer additional protection against chemotherapy drugs\*



\*see product packaging for details

### Industries

- Automotive
- Automotive Aftermarket
- Life Sciences
- Mining
- Energy
- Healthcare

### Recommended For

- General Purpose Auto Aftermarket
- Sample taking and processing
- Raw material sample collection
- Product inspection
- Vehicle maintenance
- Protection from Type I latex allergy in HCW's or patients
- Picking parts and accessories
- Handling of tools
- Inspection, selecting, checking parts
- Assembly and inspection of components
- Equipment repair and maintenance
- Administering drugs
- Inspection of primary product
- Extra protection over the wrist and arm

# TECHNICAL DATA SHEET

Product Information	
<b>Material</b>	Nitrile
<b>External Glove Surface</b>	Textured Fingers
<b>Audit Standards</b>	ISO 13485:2003
<b>Product Certification</b>	Medical Device Regulation (EU) 2017/745 Class I, Personal Protective Equipment Regulation (EU) 2016/425 Category III risks, CE 0493, European Directive 89/686/EEC, EN 455 1-4, EN ISO 374-1:2016 Type B JKT, EN ISO 374-5:2016 Virus, FDA21 CFR 177-2600-US Food Contact Approved, UKCA
<b>Packaging Overview</b>	100 gloves per dispenser 10 dispensers per case 1000 gloves per case
<b>Storage Instructions</b>	Keep out of direct sunlight; store in a cool and dry place. Keep away from sources of ozone or ignition.
<b>Country Of Origin</b>	Malaysia
<b>Product Segmentation</b>	High Risk
<b>Antistatic</b>	Yes EN1149
<b>Silicone Free</b>	No


## PHYSICAL PROPERTIES

	Typical Values		Testing Method
	BEFORE AGING	AFTER AGING	
Length (mm/inches)	270 / 10.6		ASTM D3767,EN 420
Freedom from Holes (Inspection level I)	1.5 AQL		ASTM D5151,EN 455-1
Palm Thickness (mm/mils)	0.13 / 5.1		ASTM D3767,EN 420
Finger Thickness (mm/mils)	0.20 / 7.9		ASTM D3767,EN 420
Elongation at Break (%)	≥ 500	≥ 400	ASTM D412
Force at break (N)	≥9	≥10	EN 455-2

## ORDERING INFORMATION

Size	S (6.5 - 7)	M (7.5 - 8)	L (8.5 - 9)	XL (9.5 - 10)	XXL (10.5 - 11)
Product Code	93856070	93856080	93856090	93856100	93856110

### Performance Standards and Regulatory Compliance



### For additional information visit us at [www.ansell.com](http://www.ansell.com), or call us at

#### Europe, Middle East & Africa Region

Ansell Healthcare Europe NV  
T: +32 (0) 2 528 74 00  
F: +32 (0) 2 528 74 01

#### Asia Pacific Region

MY: +603 8310 6688  
apac.medical@ansell.com  
CN: +86 21 38275000  
infochina@ansell.com  
JP: +813 5549 8151  
info.medical.jp@ansell.com

#### North America Region

Ansell Healthcare Products LLC  
T: +1 800 800 0444  
F: +1 800 800 0445

#### Latin America & Caribbean Region

BR: +55 (11) 3356-3100  
latam.medical@ansell.com  
MX: +52 442 296 2050  
latam.medical@ansell.com  
CO: +57 1 288 3247  
latam.medical@ansell.com

#### Australia

Ansell Limited  
T: +61 1800 337 041  
F: +61 1800 803 578

#### Russia

Ansell PYC  
Ten. +7 495 258 13 16

Ansell, ® and ™ are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending; [www.ansell.com/patentmarking](http://www.ansell.com/patentmarking) © 2025 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.

