

ACTIVARMR™

80-505

Medium duty thermal and cut-resistant glove with DuPont™ Kevlar™



Heat



Medium Duty

Our first ANSI/ISEA 105 Cut A5 & conductive heat resistant level 2* glove offering uncompromising comfort and dexterity

- **Enhanced protection:** Designed with Dupont™ Kevlar™ engineered yarn and Ansell INTERCEPT™ technology, these nitrile foam coated gloves meet ANSI A5/EN ISO E cut protection levels, for improved workplace safety
- **Reliable conductive heat resistant:** ActivArmr 80-505 satisfy ANSI/ISEA 105 conductive heat resistant level 2/EN 407 contact heat level 1 requirements, enabling workers to handle hot components upto 140°C/284°F for 15 secs
- **Improved durability:** Thumb-crotch reinforcement technology and a dirt-masking design extend glove life
- **Touchscreen compatible:** Allows the wearer to work with multiple touchscreen devices while keeping gloves on



Industries

- Automotive
- Metal fabrication
- Energy
- Automotive Aftermarket
- Chemical
- Mining
- Aerospace

Applications

- Handling metal sheets & panels
- Handling materials with sharp or rough edges
- Handling molded structural parts
- Metalworking & assembly operations
- Machine tool operation
- Cutting glasses, sheets, panels
- General maintenance

WWW.ANSELL.COM

Ansell

ACTIVARMR™

80-505

Medium duty thermal and cut-resistant glove with DuPont™ Kevlar™

Key Features

- ♦ Kevlar™ engineered yarn and Ansell INTERCEPT™ to achieve ANSI A5/ EN ISO E cut protection
- ♦ ANSI/ISEA 105 conductive heat resistant level 2: Protects up to 140°C/284°F
- ♦ Thumb crotch reinforcement for longer wear and dexterous comfort
- ♦ Compliant with US FDA 21 CFR 177 ". The glove is safe to contact with dry food.

Technologies

 **INTERCEPT™**
Cut Resistance Technology

 **Touchscreen Compatible**

Performance Standards & Regulatory Compliance

ANSI/ISEA 105-2024



EN388: 2016



4X32E

EN 407



X1XXXX

Specifications

BRAND STYLE	DESCRIPTION	Gauge	SIZE	LENGTH	COATING COLOR	PACKAGE
ActivArm™ 80-505	Finishing: Palm Coated, Thumbcrotch reinforcement Coating Material: Foam Nitrile Liner Material: Steel fiber, Basalt, Polyester, Spandex, Kevlar® Cuff Style: Elasticized knitted wrist	13	6, 7, 8, 9, 10, 11, 12	215-290 mm / 8.46-11.41 inches	Black	• 12 pairs/paper band; 12 paper bands/carton

For additional information visit us at www.ansell.com, or call us at

Europe, Middle East & Africa Region

Ansell Healthcare Europe NV
Riverside Business Park
Blvd International, 55
1070 Brussels, Belgium
T: +32 (0) 2 528 74 00
F: +32 (0) 2 528 74 01

North America Region

Ansell Healthcare Products LLC
111 Wood Avenue South,
Suite 900
Iselin, NJ 08830, USA
T: +1 800 800 0444
F: +1 800 800 0445

Australia

Ansell Limited
Level 3, 678 Victoria Street,
Richmond, Vic, 3121
Australia
T: +61 1800 337 041
F: +61 1800 803 578

Asia Pacific Region

Ansell Global Trading Center
(Malaysia) Sdn Bhd
Prima 6, Prima Avenue
Block 3512, Jalan Teknokrat 6
T: +603 8310 6688
F: +603 8310 6699

Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.
Blvd. Bernardo Quintana No. 7001-C,
Q7001 Torre II,
Suites 1304, 1305 y 1306,
Col. Centro Sur, c.p. 76079
Queretaro, Qro. Mexico
T: +52 442 248 1544 / 248 3133

Canada

Ansell Canada
105 Lauder
Cowansville, QC J2K 2K8
Canada
T: +1 800 363 8340
F: +1 800 267 3551

Ansell, ® and ™ are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending: www.ansell.com/patentmarking © 2025 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.

Ansell