



S-BCRL

Sterile Cut Resistance Cleanroom Liner

Sterile glove liners that offer comfort, dexterity and heightened cut resistance

- **Advanced defenses:** The BioClean™ Cut Resistant Liner S-BCRL features innovative Dyneema™ Diamond yarn, resulting in heightened cut resistance
- **Specialized protection:** These glove liners comply with ANSI/ISEA 105-2024 CUT A2 and EN ISO B standards, ensuring safe handling of sharp objects.
- **Sterility assurance:** These ambidextrous glove liners also boast an SAL (Sterility Assurance Level) of 10^{-6} , for reduced contamination risks
- **Improved fit:** The BioClean™ Cut Resistant Liner S-BCRL are specially designed to be worn between two cleanroom gloves



KEY FEATURES & BENEFITS

- ◊ **Dyneema™ Diamond yarn:** For glove liners with robust cut protection
- ◊ **Compliant with ANSI/ISEA 105-2024 CUT A2 and EN ISO B standards:** ensuring safe handling of sharp objects.
- ◊ **SAL (Sterility Assurance Level) of 10^{-6} :** Reduced contamination risks

WARNING: No liner provides complete protection against cuts. Use care when handling sharp objects.

Industries

- Controlled and Critical Environments
- Laboratory and Research
- Production and Manufacturing
- Sterile Processing Department



S-BCRL

Sterile Cut Resistance Cleanroom Liner

TECHNICAL DATA SHEET

	Product Information
Color	Yellow, Green, Orange, Blue, Red
Shape	Ambidextrous
Regulatory/Standard Compliance	ANSI/ISEA 105-2024, EN 420:2003 + A1:2009, EN 388:2016, ISO 11137-1:2006, Category II
Packaging	1 pair per inner PE wallet; one wallet per sealed EasyTear PE pouch; 10 pouches per sealed outer PE bag; 10 outer bags per lined carton (100 pairs).
Available sizes	XS (5.5 - 6), S (6.5 - 7), M (7.5 - 8), L (8.5 - 9), XL (9.5 - 10)
Sterilization Method	GAMMA irradiation (25 kGy)
Sterilization Minimum Dose	25kGy
Sterility Assurance Level	10 ⁻⁶
Cleanroom Class	Class 10/ISO Class 4, EU GMP Grade A/B and other sterile cleanrooms
Shelf Life	5 Years
Tested for use with Chemotherapy Drugs	No



S-BCRL

Sterile Cut Resistance Cleanroom Liner

Physical Properties						Testing Method
Sizes	XS (5.5 - 6)	S (6.5 - 7)	M (7.5 - 8)	L (8.5 - 9)	XL (9.5 - 10)	EN 420
Typical Length (mm/in)	XS-162 / 6.3, S-174 / 6.8, M-182 / 7.1, L-192 / 7.5, XL- 202 / 7.9					
Palm Width (mm/in)	70/2.7	72/2.8	75/2.9	79/3.1	85/3.3	

ORDERING INFORMATION

SIZE	XS (5.5 - 6)	S (6.5 - 7)	M (7.5 - 8)	L (8.5 - 9)	XL (9.5 - 10)
REORDER NO.	S-BCRL-5055	S-BCRL-6065	S-BCRL-7075	S-BCRL-8085	S-BCRL-9090

PERFORMANCE STANDARDS AND REGULATORY COMPLIANCE



For additional information visit us at www.ansell.com, or call us at

Europe, Middle East & Africa Region

Ansell Healthcare Europe NV
T: +32 (0) 2 528 74 00
F: +32 (0) 2 528 74 01

Asia Pacific Region

Ansell Global Trading Center
T: +603 8310 6688
F: +603 8310 6699

North America Region

Ansell Healthcare Products LLC
US T: +1 800 800 0444
US F: +1 800 800 0445
CA T: +1-800-363-8340

Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.
T: +52 442 248 1544 / 248 3133

Australia

Ansell Limited
T: +61 1800 337 041
F: +61 1800 803 578

UK

Ansell Nitritex
T: +44 1638 663338
F: +44 1638 668890

Ansell, ® and ™ are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending:
www.ansell.com/patentmarking © 2025 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.

