

HyFlex™

11-561

Ultra-light cut protection for 2x longer wear



Cut



Light Duty

Ultra-light ANSI/ISEA 105-2024 A3/ EN ISO C cut protection with FORTIX™ for 2x wear*

- **Increased durability for extended use:** Improved FORTIX™ Technology delivers 2x more abrasion resistance for longer-lasting performance in abrasive conditions*
- **Enhanced comfort:** HyFlex™ 11-561 features an ultra-lightweight design, 20% lighter while meeting ANSI/ISEA 105-2024 CUT A3 and EN ISO cut level C standards**
- **Heightened defenses:** 2x greater cut resistance*** using next-gen single HPPE yarn with INTERCEPT™ Cut Resistance Technology for high-performance protection
- **Excellent grip:** Palm-dipped coating improves grip, while reinforced thumb crotch defends against rapid wear
- **Touchscreen compatible:** Enables use of touchscreen devices without removing gloves

* Comparison is based on Ansell lab tests under standardized conditions in December 2025 versus similar competitive gloves. Results may vary by application.

** Versus standard ANSI/ISEA 105-2024 CUT A3 and EN ISO C rated gloves

*** Versus similar gloves made of standard HPPE yarn



Industries

- Automotive
- Manufacturing

Applications

- Assembly of sharp parts
- Handling sharp metal parts
- Light duty stamping
- Maintenance
- Compatible with consumer and industrial touchscreens
- Assembly & inspection of components
- Applying finish to materials, products

HyFlex™

11-561

Ultra-light cut protection for 2x longer wear

Key Features

- ♦ **Longer wear life:** Improved FORTIX™ Technology for 2x longer use*
- ♦ **Ultra-light design:** 20% lighter for greater dexterity**
- ♦ **Comfort & convenience:** Touchscreen compatible, all-day comfort

* Comparison is based on Ansell lab tests under standardized conditions in December 2025 versus similar competitive gloves. Results may vary by application.

** Versus standard ANSI/ISEA 105-2024 CUT A3 and EN ISO C rated gloves.

Technologies



DMF free



Fibre glass free



FORTIX™

Abrasion Resistance Technology



INTERCEPT™

Cut Resistance Technology



Performance Standards & Regulatory Compliance

ANSI/ISEA 105-2024



EN388: 2016



4X42C

EN 407



X1XXXX



STANDARD 100

1408033

Specifications

BRAND STYLE	DESCRIPTION	Gauge	SIZE	LENGTH	COATING COLOR	PACKAGE
HyFlex™ 11-561	Finishing: Palm Coated, Thumbcrotch reinforcement Coating Material: Nitrile Liner Material: INTERCEPT™ Cut Resistance Technology Cuff Style: Knitwrist	15	5, 6, 7, 8, 9, 10, 11, 12	210-285 mm / 8.27-11.22 inches	Grey	• 12 pairs/bag, 12 bags/carton

For additional information visit us at www.ansell.com, or call us at

Europe, Middle East & Africa Region

Ansell Healthcare Europe NV
Riverside Business Park
Blvd International, 55
1070 Brussels, Belgium
T: +32 (0) 2 528 74 00
F: +32 (0) 2 528 74 01

Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.
Blvd. Bernardo Quintana No. 7001-C,
Q7001 Torre II,
Suites 1304, 1305 y 1306,
Col. Centro Sur, c.p. 76079
Queretaro, Qro. Mexico
T: +52 442 248 1544 / 248 3133

North America Region

Ansell Healthcare Products LLC
111 Wood Avenue South,
Suite 900
Iselin, NJ 08830, USA
T: +1 800 800 0444
F: +1 800 800 0445

Canada

Ansell Canada
105 Lauder
Cowansville, QC J2K 2K8
Canada
T: +1 800 363 8340
F: +1 800 267 3551

Australia

Ansell Limited
Level 3, 678 Victoria Street,
Richmond, Vic, 3121
Australia
T: +61 1800 337 041
F: +61 1800 803 578

Asia Pacific Region

Ansell Global Trading Center
(Malaysia) Sdn Bhd
Prima 6, Prima Avenue
Block 3512, Jalan Teknokrat 6
T: +603 8310 6688
F: +603 8310 6699