



Cut



Light Duty

Our lightest EN ISO CUT C & ANSI/ISEA 105-2024 CUT A3 glove* offering 2 times greater cut resistance**

- **Enhanced comfort:** Ultra-lightweight design of HyFlex® 11-561 makes this EN ISO CUT C & ANSI/ISEA 105-2024 A3-rated safety glove 20% lighter*
- **Heightened defenses:** 2 times greater cut resistance** using Next Generation single HPPE yarn developed with INTERCEPT™ Cut Resistance Technology for reliable hand protection
- **Increased durability for extended use:** Improved FORTIX™ Technology delivers up to 20% more abrasion resistance for longer lasting handling in abrasive conditions***
- **Excellent grip:** HyFlex 11-561's palm-dipped coating improves grip, while a reinforced thumb crotch defends against rapid wear
- **Certified harm-free:** Dermatest® and Oeko-Tex® certification ensures these PPE gloves are skin-friendly and free of harmful substances
- **Touchscreen compatible:** Allows the wearer to work with multiple touchscreen devices while keeping gloves on

* Versus standard EN CUT ISO C & ANSI/ISEA 105-2024 CUT A3-rated gloves

** Versus similar gloves made of standard HPPE yarn

*** Versus previous technology version



Industries

- Automotive
- Machinery and Equipment
- Metal fabrication
- Mining
- Oil and gas
- Automotive Aftermarket

Applications

- Handling metal sheets & panels
- Handling parts with sharp, rough edges
- Final assembly
- Handling materials with sharp or rough edges
- Assembly & inspection of components
- Applying finish to materials, products
- Compatible with consumer and industrial touchscreens

Key Features

- **Ultra-lightweight design:** 20% lighter* for unparalleled comfort and dexterity
- **EN CUT ISO C & ANSI/ ISEA 105-2024 CUT A3 protection:** 2x greater cut resistance**
- **Improved FORTIX™ Technology:** up to 20% greater durability***
 - * Versus standard EN CUT ISO C & ANSI/ISEA 105-2024 CUT A3 gloves
 - ** Versus similar gloves made of standard HPPE yarn
 - *** Versus previous technology version

Technologies



DMF free



Fibre glass free



FORTIX™

Abrasion Resistance Technology



INTERCEPT™

Cut Resistance Technology



Performance Standards & Regulatory Compliance



4X42C



4X42C



STANDARD 100
1408033
Centexbel

Specifications

BRAND STYLE	DESCRIPTION	Gauge	SIZE	LENGTH	COATING COLOR	PACKAGE
HyFlex® 11-561	Finishing: Palm Coated Coating Material: Nitrile Liner Material: Nylon, HPPE, Basalt, Spandex, Polyester Cuff Style: Knitwrist	15	5, 6, 7, 8, 9, 10, 11, 12	210-285 mm	Grey	12 pairs/bag, 12 bags/carton

For additional information visit us at www.ansell.com, or call us at

Europe, Middle East & Africa Region
Ansell Healthcare Europe NV
Riverside Business Park
Blvd International, 55
1070 Brussels, Belgium
T: +32 (0) 2 528 74 00
F: +32 (0) 2 528 74 01

Latin America & Caribbean Region
Ansell Commercial Mexico S.A. de C.V.
Blvd. Bernardo Quintana No. 7001-C,
Q7001 Torre II,
Suites 1304, 1305 y 1306,
Col. Centro Sur, c.p. 76079
Queretaro, Qro. Mexico
T: +52 442 248 1544 / 248 3133

North America Region
Ansell Healthcare Products LLC
111 Wood Avenue South,
Suite 900
Iselin, NJ 08830, USA
T: +1 800 800 0444
F: +1 800 800 0445

Canada
Ansell Canada
105 Lauder
Cowansville, QC J2K 2K8
Canada
T: +1 800 363 8340
F: +1 800 267 3551

Australia
Ansell Limited
Level 3, 678 Victoria Street,
Richmond, Vic, 3121
Australia
T: +61 1800 337 041
F: +61 1800 803 578

Asia Pacific Region
Ansell Global Trading Center
(Malaysia) Sdn Bhd
Prima 6, Prima Avenue
Block 3512, Jalan Teknokrat 6
T: +603 8310 6688
F: +603 8310 6699

Ansell, ® and ™ are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending: www.ansell.com/patentmarking © 2024 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.