

# HyFlex™

## 11-571

Ultra-light cut protection for >2x longer wear



Cut



Light Duty

## Ultra-light ANSI/ISEA 105-2024 A4/ EN ISO D cut protection with FORTIX™ for >2x longer-lasting performance

- **Increased durability for extended use:** Improved FORTIX™ Technology delivers more than 2 times abrasion resistance for longer lasting handling in abrasive conditions\*
- **Enhanced comfort:** The ultra-lightweight design of the HyFlex™ 11-571 makes this ANSI/ISEA 105-2024 CUT A4 and EN ISO cut level D industrial glove 20% lighter\*\* without harsh materials
- **Heightened defenses:** 3 times greater cut resistance\*\*\* using Next Generation single HPPE yarn developed with INTERCEPT™ Cut Resistance Technology for reliable hand protection
- **Excellent grip:** Palm-dipped coating improves grip, while reinforced thumb crotch defends against rapid wear
- **Touchscreen Compatible/ ESD:** Allows the wearer to work multiple touchscreen devices while keeping gloves on

\* Comparison is based on Ansell lab tests under standardized conditions in December 2025 versus similar competitive gloves. Results may vary by application.

\*\* Versus standard ANSI/ISEA 105-2024 CUT A4 and EN ISO D rated gloves

\*\*\* Versus similar gloves made of standard HPPE yarn



### Industries

- Automotive
- Manufacturing

### Applications

- Light duty stamping
- Maintenance
- Handling sharp metal parts
- Assembly of sharp parts

# HyFlex™

## 11-571

Ultra-light cut protection for >2x longer wear

### Key Features

- ◊ **Longer wear life:** Improved FORTIX™ Technology for >2x longer use\*
- ◊ **Ultra-light design:** 20% lighter for greater dexterity\*\*
- ◊ **Comfort & convenience:** Touchscreen compatible, all-day comfort

\* Comparison is based on Ansell lab tests under standardized conditions in December 2025 versus similar competitive gloves. Results may vary by application.

\*\* Versus standard ANSI/ISEA 105-2024 CUT A4 and EN ISO D gloves.

### Technologies

 **FORTIX™**  
Abrasion Resistance Technology

 **INTERCEPT™**  
Cut Resistance Technology



**Touchscreen Compatible**



DMF free

### Performance Standards & Regulatory Compliance



### Specifications

BRAND   STYLE	DESCRIPTION	Gauge	SIZE	LENGTH	COATING COLOR	PACKAGE
HyFlex™ 11-571	<b>Finishing:</b> Palm dipped, Thumbcrotch reinforcement <b>Coating Material:</b> Nitrile <b>Liner Material:</b> INTERCEPT™ reinforced HPPE yarn <b>Cuff Style:</b> Knitwrist	15	5, 6, 7, 8, 9, 10, 11, 12	195-265 mm / 7.67-10.43 inches	Black	• 12 pairs/bag, 12 bags/carton

For additional information visit us at [www.ansell.com](http://www.ansell.com), or call us at

**Europe, Middle East & Africa Region**  
Ansell Healthcare Europe NV  
Riverside Business Park  
Blvd International, 55  
1070 Brussels, Belgium  
T: +32 (0) 2 528 74 00  
F: +32 (0) 2 528 74 01

**Latin America & Caribbean Region**  
Ansell Commercial Mexico S.A. de C.V.  
Blvd. Bernardo Quintana No. 7001-C,  
Q7001 Torre II,  
Suites 1304, 1305 y 1306,  
Col. Centro Sur, c.p. 76079  
Queretaro, Qro. Mexico  
T: +52 442 248 1544 / 248 3133

**North America Region**  
Ansell Healthcare Products LLC  
111 Wood Avenue South,  
Suite 900  
Iselin, NJ 08830, USA  
T: +1 800 800 0444  
F: +1 800 800 0445

**Canada**  
Ansell Canada  
105 Lauder  
Cowansville, QC J2K 2K8  
Canada  
T: +1 800 363 8340  
F: +1 800 267 3551

**Australia**  
Ansell Limited  
Level 3,678 Victoria Street,  
Richmond, Vic, 3121  
Australia  
T: +61 1800 337 041  
F: +61 1800 803 578

**Asia Pacific Region**  
Ansell Global Trading Center  
(Malaysia) Sdn Bhd  
Prima 6, Prima Avenue  
Block 3512, Jalan Teknokrat 6  
T: +603 8310 6688  
F: +603 8310 6699