



Cut



Light Duty

## Boosts precision and productivity with second-skin comfort in an ANSI A4/ISO D-rated glove

- **Second-Skin Design:** Engineered with AEROFIT™ Technology, an innovative, flexible foam nitrile coating delivering improved control and tactility – **94% of glove wearers reported improved fingertip control and tactile sensitivity\***.
- **Premium Comfort:** **98% of professionals preferred** HyFlex 11-574 for **precision handling** tasks and **all-day wear\***.
- **Proven Productivity:** Users wearing HyFlex 11-574 safety gloves **completed precision tasks 42% faster\***.
- **Advanced Cut Protection:** Features next generation INTERCEPT™ reinforced HPPE yarn for reliable ANSI/ISEA 105-2024 A4/ EN ISO D cut resistance when handling sharp or rough-edged objects.
- **Improved Compliance:** Reduced glove removal during shifts thanks to touchscreen compatibility and certified skin-friendliness.

\* Based on a survey of 52 glove wearers comparing Ansell gloves to competitive gloves available on the market (May 2025)



### Industries

- Aerospace
- Machinery and Equipment
- Metal fabrication
- Automotive
- Food Processing

### Applications

- Assembly of small parts
- Assembly & inspection of components
- Body Surface checking, marking and touching up
- Dry food handling & packaging
- Handling parts with sharp, rough edges

# HyFlex®

ADVANCED MECHANICAL PROTECTION

## 11-574

High-tactility cut-resistant glove

### Key Features

- **AEROFIT™ Coating:** up to 30% thinner<sup>1</sup> for exceptional tactility and control.
- **Breathable 21-Gauge Liner:** 98% preferred it for all-day comfort<sup>2</sup>.
- **Productivity-Enhancing Design:** enables 42% faster precision work<sup>3</sup>.

1 Versus standard Ansell glove with the same level of protection

2 & 3 Based on a survey of 52 glove wearers comparing Ansell gloves to the competitive gloves available on the market (May 2025)

### Technologies



DMF free



### Performance Standards & Regulatory Compliance

ANSI/ISEA 105-2024



EN388: 2016



3X31D



STANDARD 100

1408033  
Centexbel

### Specifications

BRAND   STYLE	DESCRIPTION	Gauge	SIZE	LENGTH	COATING COLOR	PACKAGE
HyFlex® 11-574	<b>Finishing:</b> Palm Coated <b>Coating Material:</b> Foam Nitrile <b>Liner Material:</b> HPPE, Nylon, Natural Rubber Latex, Polyester, Spandex <b>Cuff Style:</b> Knitwrist	21	5, 6, 7, 8, 9, 10, 11, 12	229-279 mm/9-11 inches	Black	12 pairs/paper band, 12 paper bands/carton

For additional information visit us at [www.ansell.com](http://www.ansell.com), or call us at

#### Europe, Middle East & Africa Region

Ansell Healthcare Europe NV  
Riverside Business Park  
Blvd International, 55  
1070 Brussels, Belgium  
T: +32 (0) 2 528 74 00  
F: +32 (0) 2 528 74 01

#### Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.  
Blvd. Bernardo Quintana No. 7001-C,  
Q7001 Torre II,  
Suites 1304, 1305 y 1306,  
Col. Centro Sur, c.p. 76079  
Queretaro, Qro. Mexico  
T: +52 442 248 1544 / 248 3133

#### North America Region

Ansell Healthcare Products LLC  
111 Wood Avenue South,  
Suite 900  
Iselin, NJ 08830, USA  
T: +1 800 800 0444  
F: +1 800 800 0445

#### Canada

Ansell Canada  
105 Lauder  
Cowansville, QC J2K 2K8  
Canada  
T: +1 800 363 8340  
F: +1 800 267 3551

#### Australia

Ansell Limited  
Level 3, 678 Victoria Street,  
Richmond, Vic, 3121  
Australia  
T: +61 1800 337 041  
F: +61 1800 803 578

#### Asia Pacific Region

Ansell Global Trading Center  
(Malaysia) Sdn Bhd  
Prima 6, Prima Avenue  
Block 3512, Jalan Teknokrat 6  
T: +603 8310 6688  
F: +603 8310 6699