

ACTIVARMR™

97-013

Medium duty increased visibility glove



Cut



Medium Duty

Durable increased visibility work gloves, designed to protect workers in low-light conditions

- **Specialized protection:** ActivArm™ 97-013 industrial gloves possess high-visibility features on the palm and back of the hand, with a retro-reflective logo, to ensure wearer safety in dark/low-light conditions
- **Optimized comfort:** With a 13-gauge fiberglass and polyester liner, ActivArm™ 97-013 safety work gloves keep hands comfortable and sweat-free throughout the day
- **Advanced ergonomics:** These hand protection gloves offer a naturally curved, relaxed fit, for reduced hand fatigue and increased dexterity
- **Improved cut resistance:** They are also designed with INTERCEPT™ Cut Resistance Technology, for better laceration defenses
- **Added grip:** ActivArm™ 97-013 medium-duty gloves boast excellent grip in both wet and dry working environments



Industries

- Energy
- Mining

Applications

- Signalling/Positioning
- Operating of heavy machinery
- Loading and hauling
- Hydraulic repair
- Shipping and loading of product
- Vehicle Maintenance
- General pumping work
- Preparation of site - set-up and disassembly of tool string
- Set-up of pressure manifold and tubing injector head
- Handling of tools
- Valve - line maintenance and repair
- Handling jagged metal
- Equipment maintenance Scaffolding Pipe handling and insulation Plumbing and sand blasting
- Heavy machine operation

ACTIVARMR™

97-013

Medium duty increased visibility glove

Key Features

- ♦ **Extra visibility back and palm:** Protecting hands in dark environments
- ♦ **13-gauge fiberglass and polyester liner:** Sweat-proof all-day comfort
- ♦ **Ergonomic design:** Naturally curved fit, for reduced hand fatigue

Performance Standards & Regulatory Compliance



ANSI/ISEA 105-2024



EN388: 2016



4X32B

Technologies



INTERCEPT™
Cut Resistance Technology

Specifications

BRAND STYLE	DESCRIPTION	Gauge	SIZE	LENGTH	COATING COLOR	PACKAGE
ActivArm™ 97-013	Finishing: Palm Coated Coating Material: Water-Based polyurethane and nitrile Liner Material: Fiber glass, Polyester Cuff Style: Knitwrist	13	7, 8, 9, 10, 11	240-280 mm / 9.45-11.02 inches	Orange	• 12 pairs/bag, 6 bags/carton

For additional information visit us at www.ansell.com, or call us at

Europe, Middle East & Africa Region

Ansell Healthcare Europe NV
Riverside Business Park
Blvd International, 55
1070 Brussels, Belgium
T: +32 (0) 2 528 74 00
F: +32 (0) 2 528 74 01

North America Region

Ansell Healthcare Products LLC
111 Wood Avenue South,
Suite 900
Iselin, NJ 08830, USA
T: +1 800 800 0444
F: +1 800 800 0445

Australia

Ansell Limited
Level 3, 678 Victoria Street,
Richmond, Vic, 3121
Australia
T: +61 1800 337 041
F: +61 1800 803 578

Asia Pacific Region

Ansell Global Trading Center
(Malaysia) Sdn Bhd
Prima 6, Prima Avenue
Block 3512, Jalan Teknokrat 6
T: +603 8310 6688
F: +603 8310 6699

Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.
Blvd. Bernardo Quintana No. 7001-C,
Q7001 Torre II,
Suites 1304, 1305 y 1306,
Col. Centro Sur, c.p. 76079
Queretaro, Qro. Mexico
T: +52 442 248 1544 / 248 3133

Canada

Ansell Canada
105 Lauder
Cowansville, QC J2K 2K8
Canada
T: +1 800 363 8340
F: +1 800 267 3551

Ansell, ® and ™ are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending: www.ansell.com/patentmarking © 2025 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.

Ansell