



Cut

## Durable polyurethane gloves with a lightweight liner, for flexibility and tactility

- **Heightened flexibility:** HyFlex® 11-731 polyurethane gloves' lightweight 18-gauge liner enhances their flexibility and tactility
- **Enhanced durability:** These safety gloves' light PU coating offers greater dexterity and makes them more abrasion-resistant, for EN level 4 and ANSI level 3 abrasion protection
- **Improved defenses:** HyFlex® 11-731 industrial safety gloves' INTERCEPT™ Cut Resistance Technology yarn grant them added lacerations defenses, with EN ISO B/ANSI A2 protection
- **Considered aesthetics:** Dirt-masking color treatment on these HyFlex gloves' coating hides stains and marks, ensuring longer glove life
- **Guaranteed convenience:** These PPE gloves are also available in vend pack form, for simplified access to personal protection



### Industries

- Automotive
- Machinery and Equipment
- Metal fabrication
- Transportation

### Applications

- Assembly & inspection of components
- Press injection molding
- Picking, fastening components
- Final assembly
- Delivery of parts to production line
- Applying finish to materials, products
- Handling incoming goods

### Key Features

- **Light 18-gauge liner:** Greater flexibility and tactile sensitivity
- **Thin PU coating:** Durable industrial gloves with strengthened grip
- **INTERCEPT™ Cut Resistance:** For reliable personal protection

### Vulcanization Chemical Accelerators

- Natural rubber proteins (in knitwrist elastic)

Only a very small number of users may be sensitive to this ingredient(s) and hence may develop irritant and/or allergic contact reactions.

### Performance Standards & Regulatory Compliance



### Technologies



### Specifications

| BRAND   STYLE  | DESCRIPTION                                                                                                                                                        | Gauge | SIZE               | LENGTH                      | COATING COLOR | PACKAGE                        |
|----------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------|-------|--------------------|-----------------------------|---------------|--------------------------------|
| HyFlex® 11-731 | <b>Finishing:</b> Palm Coated<br><b>Coating Material:</b> Polyurethane<br><b>Liner Material:</b> Fiber glass, HPPE, Nylon, Spandex<br><b>Cuff Style:</b> Knitwrist | 18    | 6, 7, 8, 9, 10, 11 | 212-277 mm/ 8,34-10,43 inch | Grey          | • 12 pairs/bag; 12 bags/carton |

For additional information visit us at [www.ansell.com](http://www.ansell.com), or call us at

#### Europe, Middle East & Africa Region

Ansell Healthcare Europe NV  
Riverside Business Park  
Blvd International, 55  
1070 Brussels, Belgium  
T: +32 (0) 2 528 74 00  
F: +32 (0) 2 528 74 01

#### Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.  
Blvd. Bernardo Quintana No. 7001-C,  
Q7001 Torre II,  
Suites 1304, 1305 y 1306,  
Col. Centro Sur, c.p. 76079  
Queretaro, Qro. Mexico  
T: +52 442 248 1544 / 248 3133

#### North America Region

Ansell Healthcare Products LLC  
111 Wood Avenue South,  
Suite 900  
Iselin, NJ 08830, USA  
T: +1 800 800 0444  
F: +1 800 800 0445

#### Canada

Ansell Canada  
105 Lauder  
Cowansville, QC J2K 2K8  
Canada  
T: +1 800 363 8340  
F: +1 800 267 3551

#### Australia

Ansell Limited  
Level 3, 678 Victoria Street,  
Richmond, Vic, 3121  
Australia  
T: +61 1800 337 041  
F: +61 1800 803 578

#### Asia Pacific Region

Ansell Global Trading Center  
(Malaysia) Sdn Bhd  
Prima 6, Prima Avenue  
Block 3512, Jalan Teknokrat 6  
T: +603 8310 6688  
F: +603 8310 6699