

# Sensilite®

## 48-100

Designed for light applications that require good levels of comfort and abrasion resistance

Previously known as: Sensilite



Multi Purpose



Cut



Light Duty

## White multi-purpose polyurethane gloves, designed with comfortable light duty handling in mind

- **Improved durability:** HyFlex™ 48-100 industrial work gloves feature ANSI/ISEA and EN compliant abrasion resistance levels
- **Augmented dexterity:** Their thin, flexible nylon liner makes for dexterous, strain-free everyday use
- **White color:** The lighter tone of these HyFlex™ gloves ensures process quality and helps avoid cross contamination
- **Optimized tactility:** HyFlex™ 48-100 PPE gloves' palm-dipped PU coating results in high levels of tactile sensitivity, for precision handling in dry or slightly oily conditions
- **Genuine versatility:** Light, resilient and tactile, HyFlex™ 48-100 industrial gloves are used for a multitude of diverse applications



### Industries

- Automotive

### Applications

- Chassis assembly, body trimming
- Production line support & maintenance
- Equipment repair & maintenance
- Assembly and disassembly of equipment
- Loading and unloading rough parts or boxes
- Picking parts and accessories

# Sensilite®

## 48-100

Designed for light applications that require good levels of comfort and abrasion resistance

Previously known as: Sensilite

### Key Features

- ♦ **Palm-dipped PU coating:** ANSI/ISEA and EN compliant abrasion resistance
- ♦ **Thin nylon liner:** Dexterous comfort for light-duty applications
- ♦ **White color:** Process safe PPE gloves that avoid cross contamination

### Vulcanization Chemical Accelerators

- Natural rubber proteins

Only a very small number of users may be sensitive to this ingredient(s) and hence may develop irritant and/or allergic contact reactions.

### Performance Standards & Regulatory Compliance



### Specifications

BRAND   STYLE	DESCRIPTION	Gauge	SIZE	LENGTH	COATING COLOR	PACKAGE
HyFlex™ 48-100	<b>Finishing:</b> Palm Coated <b>Coating Material:</b> Polyurethane <b>Liner Material:</b> Nylon <b>Cuff Style:</b> Knitwrist	13	6, 7, 8, 9, 10, 11	220-270 mm / 8.66-10.63 inches	White	• 12 pairs/bag, 12 bags/carton

For additional information visit us at [www.ansell.com](http://www.ansell.com), or call us at

#### Europe, Middle East & Africa Region

Ansell Healthcare Europe NV  
Riverside Business Park  
Blvd International, 55  
1070 Brussels, Belgium  
T: +32 (0) 2 528 74 00  
F: +32 (0) 2 528 74 01

#### North America Region

Ansell Healthcare Products LLC  
111 Wood Avenue South,  
Suite 900  
Iselin, NJ 08830, USA  
T: +1 800 800 0444  
F: +1 800 800 0445

#### Australia

Ansell Limited  
Level 3,678 Victoria Street,  
Richmond, Vic, 3121  
Australia  
T: +61 1800 337 041  
F: +61 1800 803 578

#### Asia Pacific Region

Ansell Global Trading Center  
(Malaysia) Sdn Bhd  
Prima 6, Prima Avenue  
Block 3512, Jalan Teknokrat 6  
T: +603 8310 6688  
F: +603 8310 6699

#### Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.  
Blvd. Bernardo Quintana No. 7001-C,  
Q7001 Torre II,  
Suites 1304, 1305 y 1306,  
Col. Centro Sur, c.p. 76079  
Queretaro, Qro. Mexico  
T: +52 442 248 1544 / 248 3133

#### Canada

Ansell Canada  
105 Lauder  
Cowansville, QC J2K 2K8  
Canada  
T: +1 800 363 8340  
F: +1 800 267 3551

Ansell, ® and ™ are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending: [www.ansell.com/patentmarking](http://www.ansell.com/patentmarking) © 2025 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.

