

# HyFlex™

## 74-500

Highest cut level food certified glove



Cut



Medium Duty

## Highly cut-resistant ambidextrous industrial gloves, ideal for food handling applications

- **Advanced defenses:** HyFlex™ 74-500 safety gloves' liner blends fiber glass, stainless steel, HPPE, polyamide, and polyester with INTERCEPT™ Cut Resistance Technology, for advanced 360° protection
- **Improved durability:** These abrasion-resistant gloves remain durable and maintain performance levels even with repeated laundering, while also masking stains thanks to their blue color, extending overall wear life
- **Food handling compliance:** Compliant with FDA food handling regulations 21 CFR 177.1520 and 21 CFR 177.2600, these HyFlex™ gloves are suited to various food processing applications
- **Genuine practicality:** Comfortable by nature, they also boast an ambidextrous design, for greater everyday ease of use



### Industries

- Food Processing

### Applications

- Dairy Processing
- Fruit and Vegetable Processing
- Poultry Processing

# HyFlex™

## 74-500

Highest cut level food certified glove

### Key Features

- ♦ **Fiber glass- and stainless steel-infused liner:** Superb cut resistance
- ♦ **Durable materials:** Heightened abrasion resistance, longer wear life\*
- ♦ **FDA food handling compliance:** Suitable for varied food processing  
\*7x more durable than close competitors

### Performance Standards & Regulatory Compliance

ANSI/ISEA 105-2024



EN388: 2016



4X4XF

EN 388



4X4XF



### Specifications

| BRAND   STYLE  | DESCRIPTION                                                                                                                                   | Gauge | SIZE            | LENGTH                   | PACKAGE                      |
|----------------|-----------------------------------------------------------------------------------------------------------------------------------------------|-------|-----------------|--------------------------|------------------------------|
| HyFlex™ 74-500 | <b>Liner Material:</b> HPPE, Fiber glass, Stainless steel, Polyamide, Polyester, Ansell INTERCEPT™ Technology<br><b>Cuff Style:</b> Knitwrist | 10    | 7, 8, 9, 10, 11 | 230-305 mm / 9-12 inches | • 6 pairs/bag, 2 bags/carton |

For additional information visit us at [www.ansell.com](http://www.ansell.com), or call us at

#### Europe, Middle East & Africa Region

Ansell Healthcare Europe NV  
Riverside Business Park  
Blvd International, 55  
1070 Brussels, Belgium  
T: +32 (0) 2 528 74 00  
F: +32 (0) 2 528 74 01

#### Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.  
Blvd. Bernardo Quintana No. 7001-C,  
Q7001 Torre II,  
Suites 1304, 1305 y 1306,  
Col. Centro Sur, c.p. 76079  
Queretaro, Qro. Mexico  
T: +52 442 248 1544 / 248 3133

#### North America Region

Ansell Healthcare Products LLC  
111 Wood Avenue South,  
Suite 900  
Iselin, NJ 08830, USA  
T: +1 800 800 0444  
F: +1 800 800 0445

#### Canada

Ansell Canada  
105 Lauder  
Cowansville, QC J2K 2K8  
Canada  
T: +1 800 363 8340  
F: +1 800 267 3551

#### Australia

Ansell Limited  
Level 3, 678 Victoria Street,  
Richmond, Vic, 3121  
Australia  
T: +61 1800 337 041  
F: +61 1800 803 578

#### Asia Pacific Region

Ansell Global Trading Center  
(Malaysia) Sdn Bhd  
Prima 6, Prima Avenue  
Block 3512, Jalan Teknokrat 6  
T: +603 8310 6688  
F: +603 8310 6699

Ansell, ® and ™ are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending: [www.ansell.com/patentmarking](http://www.ansell.com/patentmarking) © 2025 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.

**Ansell**