

Affordable hand protection, offering excellent comfort

- **Comfortable fit:** This disposable, nitrile glove has a thin formulation for reliable protection, plus improved comfort and flexibility
- **Secure grip:** The textured fingertips of the glove provide an improved grip for a variety of applications
- **Smart packaging:** Packed with 300 gloves per dispenser box* to provide additional value and convenience

*250 pieces/dispenser for size XL



Industries

- Food Processing
- Automotive
- Life Sciences

Recommended For

- Catering/Meal preparation
- Food processing and handling
- Inspection of parts, equipment
- Assembly and inspection of components
- Equipment repair and maintenance
- Picking and fastening components
- Adjusting parts and systems
- Handling of paint/glue guns and sprayers
- Transferring liquids and solids
- Sample taking and processing

TECHNICAL DATA SHEET

	Product Information
External Glove Surface	Textured Fingers
Audit Standards	ISO 13485, ISO 9001
Product Certification	Medical Device Regulation (EU) 2017/745 Class I, Personal Protective Equipment Regulation (EU) 2016/425 Category III risks
Packaging Overview	300 gloves per dispenser, 10 dispensers per shipper, 3000 gloves per shipper **Size XL 250 pieces/dispenser, 2500 pieces/shipper
Storage Instructions	Keep out of direct sunlight; store in a cool and dry place. Keep away from sources of ozone or ignition.
Country Of Origin	China
Product Segmentation	Standard Thin
Antistatic	Not Tested
Vulcanization Chemical Accelerators	<ul style="list-style-type: none">Zinc Dibutyldithiocarbamate (ZDBC)Zinc Diethyldithiocarbamate (ZDEC) <p><i>Only a very small number of users may be sensitive to this ingredient(s) and hence may develop irritant and/or allergic contact reactions.</i></p>

PHYSICAL PROPERTIES

	Typical Values		Testing Method
Length (mm/inches)	230 / 9.1		ASTM D3767,EN 420
Freedom from Holes (Inspection level I)	1.5 AQL		ASTM D6319-10,ASTM D5151-06 (2011)
Palm Thickness (mm/mils)	0.06/2.4		ASTM D3767,EN 420
Finger Thickness (mm/mils)	0.08/3.1		ASTM D3767,EN 420
	BEFORE AGING	AFTER AGING	
Ultimate Tensile Strength (MPa)	≥ 14	≥ 14	ASTM D6319-10
Elongation at Break (%)	≥ 500	≥ 400	ASTM D6319-10
Force at break (N)	3	3	EN 455-2

ORDERING INFORMATION

Size	XS (5.5 - 6)	S (6.5 - 7)	M (7.5 - 8)	L (8.5 - 9)	XL (9.5 - 10)
Product Code	82133060	82133070	82133080	82133090	82133100

Performance Standards and Regulatory Compliance



For additional information visit us at www.ansell.com, or call us at

Europe, Middle East & Africa Region Ansell Healthcare Europe NV T: +32 (0) 2 528 74 00 F: +32 (0) 2 528 74 01 Asia Pacific Region MY +603 8310 6688 apac.medical@ansell.com CN: +86 21 38275000 infochina@ansell.com JP: +813 5549 8151 info.medical.jp@ansell.com	North America Region Ansell Healthcare Products LLC T: +1 800 800 0444 F: +1 800 800 0445 Latin America & Caribbean Region BR +55 (11) 3356-3100 latam.medical@ansell.com MX: +52 442 296 2050 latam.medical@ansell.com CO: +57 1 288 3247 latam.medical@ansell.com	Australia Ansell Limited T: +61 1800 337 041 F: +61 1800 803 578 Russia Ansell PYC Ten. +7 495 258 13 16
--	---	--

Ansell, ® and ™ are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending: www.ansell.com/patentmarking © 2024 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.

