



Cut



Medium Duty

Mechanical protection gloves granting superior cut resistance and optimal comfort

- **Heightened defenses:** HyFlex™ 11-645 protective gloves leverage INTERCEPT™ Cut Resistance Technology to deliver 2x greater cut resistance*
- **Elevated comfort:** These cut-resistant gloves provide the fit and feel of lighter protection levels while meeting ANSI/ISEA 105-2024 CUT A4 and EN ISO D safety standards
- **Improved durability:** Owing to their skin-friendly PU coating**, these hand protection gloves afford superb durability for dry and slightly oily applications
- **Added feature:** In addition, these HyFlex™ gloves allow wearer to use multiple touchscreen devices without having to remove their gloves
- **Reduced contamination risk:** As these industrial gloves are silicone-free, they prevent contaminant transfer to metal before painting
- **Guaranteed skin-friendliness:** HyFlex™ 11-645 polyurethane gloves also possess Dermatest™ and Oekotex certification

**Versus similar gloves made of standard HPPE yarn*

***Low DMF content <100ppm compared to industry standard <1000ppm*

Industries

- Automotive
- Machinery and Equipment
- Metal fabrication

Applications

- Assembly of sharp parts
- Handling metal sheets & panels
- Maintenance
- Inspection (picking, checking and marking)



HyFlex[®]

ADVANCED MECHANICAL PROTECTION

11-645

Trusted comfort with 2x more cut resistance*

Key Features

- ♦ **INTERCEPT[™] Cut Resistance Technology:** Twice the cut resistance*
- ♦ **Lighter fit and feel:** Enhanced comfort for extended use
- ♦ **PU coating**:** High durability for dry and slightly oily applications

*Versus similar gloves made of standard HPPE yarn

**Low DMF content <100ppm compared to industry standard <1000ppm

Performance Standards & Regulatory Compliance

ANSI/ISEA 105-2024



EN388: 2016



4X43D



1408033



Technologies



INTERCEPT[™]
Cut Resistance Technology



Touchscreen Compatible

Specifications

BRAND STYLE	DESCRIPTION	Gauge	SIZE	LENGTH	COATING COLOR	PACKAGE
HyFlex [™] 11-645	Finishing: Palm Coated Coating Material: Low DMF polyurethane Liner Material: Ansell INTERCEPT [™] Technology Cuff Style: Knitwrist	13	5, 6, 7, 8, 9, 10, 11, 12	207-277 mm / 8.14-10.90 inches	Black	• 12 pairs/bag, 12 bags/carton

For additional information visit us at www.ansell.com, or call us at

Europe, Middle East & Africa Region

Ansell Healthcare Europe NV
Riverside Business Park
Blvd International, 55
1070 Brussels, Belgium
T: +32 (0) 2 528 74 00
F: +32 (0) 2 528 74 01

North America Region

Ansell Healthcare Products LLC
111 Wood Avenue South,
Suite 900
Iselin, NJ 08830, USA
T: +1 800 800 0444
F: +1 800 800 0445

Australia

Ansell Limited
Level 3, 678 Victoria Street,
Richmond, Vic, 3121
Australia
T: +61 1800 337 041
F: +61 1800 803 578

Asia Pacific Region

Ansell Global Trading Center
(Malaysia) Sdn Bhd
Prima 6, Prima Avenue
Block 3512, Jalan Teknokrat 6
T: +603 8310 6688
F: +603 8310 6699

Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.
Blvd. Bernardo Quintana No. 7001-C,
Q7001 Torre II,
Suites 1304, 1305 y 1306,
Col. Centro Sur, c.p. 76079
Queretaro, Qro. Mexico
T: +52 442 248 1544 / 248 3133

Canada

Ansell Canada
105 Lauder
Cowansville, QC J2K 2K8
Canada
T: +1 800 363 8340
F: +1 800 267 3551

Ansell, ® and [™] are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending: www.ansell.com/patentmarking © 2025 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.

Ansell