

# ACTIV/ARMR™

## 70-765

Outstanding Mechanical Protection

Previously known as: Vantage®70-765



Cut

Abrasion Protection



Heat



Heavy Duty

## Advanced cut-resistant safety gloves, featuring premium leather for superior grip

- **Enhanced defenses:** These safety gloves feature an aramid fiber and reinforced thumb crotch, as well as seams relocated to the back of the fingers, to guard against minor injuries, sharp snags and punctures
- **Specialized protection:** Among the best leather work gloves available, the ActivArmr™ 70-765 is also capable of protecting hands from intermittent heat contact up to 200°C/392°F.
- **Strengthened grip:** They ensure strong, secure grip in oily environments
- **Improved durability:** ActivArmr™ 70-765 leather-palm work gloves feature a 10-gauge, mediumweight cut-resistant yarn, ensuring long-lasting use
- **Optimized comfort:** ActivArmr™ 70-765 safety gloves are not only heat-resistant, but comfortable and plaited with colored polyester and cotton



### Industries

- Automotive
- Metal fabrication

### Applications

- Handling metal sheets & panels
- Handling parts with sharp, rough edges
- Handling rough machined metal parts
- Glass repair and replacement
- Seizing rough blocs and cylinders
- Handling materials with sharp or rough edges
- Press shop operations

Previously known as: Vantage®70-765

#### Key Features

- **Double-stitched with aramid fiber:** Enhanced protection
- **Mediumweight cut-resistant yarn:** High cut protection-to-weight ratio
- **Heat-resistant design:** ANSI/ISEA 105 conductive heat resistant level 3: Intermittent heat contact up to 200°C/392°F according to ASTM F1060-18.

#### Vulcanization Chemical Accelerators

- Natural rubber proteins

Only a very small number of users may be sensitive to this ingredient(s) and hence may develop irritant and/or allergic contact reactions.

#### Performance Standards & Regulatory Compliance

ANSI/ISEA 105-2024



EN388: 2016



4X43D

EN 407



X1XXXX



#### Specifications

| BRAND   STYLE    | DESCRIPTION                                                                                                                                         | Gauge | SIZE         | LENGTH                         | COATING COLOR | PACKAGE                       |
|------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------|-------|--------------|--------------------------------|---------------|-------------------------------|
| ActivArm™ 70-765 | <b>Finishing:</b> Leather Palm<br><b>Coating Material:</b> Leather<br><b>Liner Material:</b> Nylon, Acrylic, Aramid<br><b>Cuff Style:</b> Knitwrist | 10    | 8, 9, 10, 11 | 245-275 mm / 9.64-10.82 inches | Grey          | • 12 pairs/bag, 3 bags/carton |

For additional information visit us at [www.ansell.com](http://www.ansell.com), or call us at

##### Europe, Middle East & Africa Region

Ansell Healthcare Europe NV  
Riverside Business Park  
Blvd International, 55  
1070 Brussels, Belgium  
T: +32 (0) 2 528 74 00  
F: +32 (0) 2 528 74 01

##### Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.  
Blvd. Bernardo Quintana No. 7001-C,  
Q7001 Torre II,  
Suites 1304, 1305 y 1306,  
Col. Centro Sur, c.p. 76079  
Queretaro, Qro. Mexico  
T: +52 442 248 1544 / 248 3133

##### North America Region

Ansell Healthcare Products LLC  
111 Wood Avenue South,  
Suite 900  
Iselin, NJ 08830, USA  
T: +1 800 800 0444  
F: +1 800 800 0445

##### Canada

Ansell Canada  
105 Lauder  
Cowansville, QC J2K 2K8  
Canada  
T: +1 800 363 8340  
F: +1 800 267 3551

##### Australia

Ansell Limited  
Level 3, 678 Victoria Street,  
Richmond, Vic, 3121  
Australia  
T: +61 1800 337 041  
F: +61 1800 803 578

##### Asia Pacific Region

Ansell Global Trading Center  
(Malaysia) Sdn Bhd  
Prima 6, Prima Avenue  
Block 3512, Jalan Teknokrat 6  
T: +603 8310 6688  
F: +603 8310 6699