

ACTIVARMR™

80-813

Arc Flash and Cut Protective Glove

Previously known as: PowerFlex®80-813



Heat



Cut



Electrical



Medium Duty

Comfortable flame-resistant gloves, offering advanced arc flash and cut protection

- **Specialized protection:** ActivArm[™] 80-813 heat-resistant gloves are tested against CGSB 155.20-2000 FR standards, boasting an industry-leading Arc Flash Hazard/Risk Category 1 design that guards against electrical arc flash hazards
- **Advanced defenses:** Featuring an aramid engineered composite yarn and a thin 13g knitted liner, these gloves offer ANSI/ISEA 105-2024 CUT A4 and EN ISO C protection, allowing for safe handling of sharp components.
- **Augmented dexterity:** ActivArm[™] 80-813 industrial gloves' patented technology and ergonomic design ensure superb flexibility and hand protection
- **Enhanced grip:** Thanks to their proprietary soft foam coating, they make for better grip gloves, reducing slippage and tension in the hands and guaranteeing secure grip performance in wet, oily and dry environments

Industries

- Machinery and Equipment
- Mining
- Energy
- Automotive
- Automotive Aftermarket
- Infrastructure Maintenance

Applications

- Job tasks with potential for arc-flash or flash-flame exposure
- De-energized electrical equipment panels
- Electrical equipment operation and switching_NFPA 70E_
- Facility and machinery maintenance
- Handling sharp metal or objects

ACTIVARMR™

80-813

Arc Flash and Cut Protective Glove

Previously known as: PowerFlex®80-813

Key Features

- ♦ **Flame-resistant materials:** Satisfies CGSB 155.20-2000 FR standards
- ♦ **Superior arc-flash protection:** Arc Category level 1 per ASTM F2675-22
- ♦ **Cut-resistant aramid yarn:** Advanced cut protection

Vulcanization Chemical Accelerators

- Zinc dibutyl dithiocarbamate

Only a very small number of users may be sensitive to this ingredient(s) and hence may develop irritant and/or allergic contact reactions.

Performance Standards & Regulatory Compliance

ANSI/ISEA 105-2024



EN388: 2016



2X42C

EN 407



412100

Specifications

BRAND STYLE	DESCRIPTION	Gauge	SIZE	LENGTH	COATING COLOR	PACKAGE
ActivArm™ 80-813	Finishing: Palm Coated Coating Material: Neoprene Liner Material: Fiber glass, Modacrylic, Aramid Cuff Style: Knitwrist	13	6, 7, 8, 9, 10, 11	213-262 mm / 8.38-10.31 inches	Black	• 12 pairs/bag, 12 bags/carton

For additional information visit us at www.ansell.com, or call us at

Europe, Middle East & Africa Region

Ansell Healthcare Europe NV
Riverside Business Park
Blvd International, 55
1070 Brussels, Belgium
T: +32 (0) 2 528 74 00
F: +32 (0) 2 528 74 01

Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.
Blvd. Bernardo Quintana No. 7001-C,
Q7001 Torre II,
Suites 1304, 1305 y 1306,
Col. Centro Sur, c.p. 76079
Queretaro, Qro. Mexico
T: +52 442 248 1544 / 248 3133

North America Region

Ansell Healthcare Products LLC
111 Wood Avenue South,
Suite 900
Iselin, NJ 08830, USA
T: +1 800 800 0444
F: +1 800 800 0445

Canada

Ansell Canada
105 Lauder
Cowansville, QC J2K 2K8
Canada
T: +1 800 363 8340
F: +1 800 267 3551

Australia

Ansell Limited
Level 3, 678 Victoria Street,
Richmond, Vic, 3121
Australia
T: +61 1800 337 041
F: +61 1800 803 578

Asia Pacific Region

Ansell Global Trading Center
(Malaysia) Sdn Bhd
Prima 6, Prima Avenue
Block 3512, Jalan Teknokrat 6
T: +603 8310 6688
F: +603 8310 6699

Ansell, ® and ™ are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending: www.ansell.com/patentmarking © 2025 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.

Ansell