

Chemical-resistant disposable gloves that offer tough chemical resistance and superior comfort

- **Three-layer design:** Three layers ensure superior protection against harsh chemicals
- **Thin mil design:** Designed to be thinner than standard reusable chemical-resistant gloves (7.8 mil) for protection that allows for better tactility when handling small objects and tools
- **Elevated comfort:** Soft material and ergonomic design offer outstanding fit, feel and flexibility
- **Assured quality:** Their low AQL (0.65) means minimal pinhole defect risks
- **High standards:** Meets EN 374 Type A certified in Europe and KOSHA certified in Korea



Industries

- Aerospace
- Automotive
- Automotive Aftermarket
- Life Sciences
- Chemical
- Agriculture
- Machinery and Equipment
- Metal fabrication
- Utilities
- Warehousing

Recommended For

- Inspection, selecting, checking parts
- Assembly and inspection of components
- Equipment repair and maintenance
- Production line support and maintenance
- General Purpose Auto Aftermarket
- Oil, fluids and filter change
- Blending, compounding solids and liquids
- Sample taking and processing
- Transferring liquids and solids between vessels and tanks and process equipment

TECHNICAL DATA SHEET

	Product Information
External Glove Surface	Textured Fingers
Audit Standards	ISO 9001
Product Certification	Personal Protective Equipment Regulation (EU) 2016/425 Category III risks
Packaging Overview	50 gloves per dispenser 10 dispensers per case 500 gloves per case
Storage Instructions	Keep out of direct sunlight; store in a cool and dry place. Keep away from sources of ozone or ignition.
Country Of Origin	Sri Lanka
Product Segmentation	High Risk
Antistatic	Yes EN1149
Vulcanization Chemical Accelerators	Zinc Dibutyldithiocarbamate (ZDBC) Only a very small number of users may be sensitive to this ingredient(s) and hence may develop irritant and/or allergic contact reactions.

PHYSICAL PROPERTIES

	Typical Values		Testing Method
Length (mm/inches)	≥ 285 / 11.2		ASTM D3767,EN 420
Freedom from Holes (Inspection level I)	0.65 AQL		ASTM D5151,EN 455-1
Palm Thickness (mm/mils)	0.198 / 7.9		ASTM D3767,EN 420
Finger Thickness (mm/mils)	0.20 / 7.9		ASTM D3767,EN 420
	BEFORE AGING	AFTER AGING	
Ultimate Tensile Strength (MPa)	≥ 14	≥ 14	ASTM D412 & D573
Elongation at Break (%)	≥ 500	≥ 400	ASTM D412
Force at break (N)	≥ 6	≥ 6	EN 455-2

ORDERING INFORMATION

Size	XS (5.5 - 6)	S (6.5 - 7)	M (7.5 - 8)	L (8.5 - 9)	XL (9.5 - 10)	XXL (10.5 - 11)
Product Code	93260060	93260070	93260080	93260090	93260100	93260110
Retail Pack Catalog №			93260RP080	93260RP090	93260RP100	

Performance Standards and Regulatory Compliance



For additional information visit us at www.ansell.com, or call us at

Europe, Middle East & Africa Region Ansell Healthcare Europe NV T: +32 (0) 2 528 74 00 F: +32 (0) 2 528 74 01 Asia Pacific Region MY: +603 8310 6688 apac.medical@ansell.com CN: +86 21 38275000 infochina@ansell.com JP: +813 5549 8151 info.medical.jp@ansell.com	North America Region Ansell Healthcare Products LLC T: +1 800 800 0444 F: +1 800 800 0445 Latin America & Caribbean Region BR: +55 (11) 3356-3100 latam.medical@ansell.com MX: +52 442 296 2050 latam.medical@ansell.com CO: +57 1 288 3247 latam.medical@ansell.com	Australia Ansell Limited T: +61 1800 337 041 F: +61 1800 803 578 Russia Ansell PYC Ten. +7 495 258 13 16
---	--	--

Ansell, ® and ™ are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending; www.ansell.com/patentmarking © 2024 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.

