

Previously known as: PowerFlex® 80-813



Heat



Cut



Electrical



Medium Duty

## Comfortable flame-resistant gloves, offering advanced arc flash and cut protection

- **Specialized protection:** ActivArm® 80-813 heat-resistant gloves are tested against CGSB 155.20-2000 FR standards, boasting an industry-leading Arc Flash Hazard/Risk Category 2 design that guards against electrical arc flash hazards
- **Advanced defenses:** They feature an aramid composite yarn and thin 13g knitted liner, delivering EN ISO C/ANSI A4-level cut resistance and protecting hands by enabling safe sharp component handling
- **Augmented dexterity:** ActivArm® 80-813 industrial gloves' patented technology and ergonomic design ensure superb flexibility and hand protection
- **Enhanced grip:** Thanks to their proprietary soft foam coating, they make for better grip gloves, reducing slippage and tension in the hands and guaranteeing secure grip performance in wet, oily and dry environments



#### Industries

- Machinery and Equipment
- Mining
- Oil and gas
- Automotive
- Automotive Aftermarket
- Utilities

#### Applications

- Job tasks with potential for arc-flash or flash-flame exposure
- De-energized electrical equipment panels
- Electrical equipment operation and switching\_NFPA 70E\_
- Facility and machinery maintenance
- Handling sharp metal or objects

Previously known as: PowerFlex® 80-813

#### Key Features

- **Flame-resistant materials:** Satisfies CGSB 155.20-2000 FR standards
- **Arc flash-resistant design:** ASTM F2675-13 Category 2 protection\*
- **Cut-resistant aramid yarn:** Advanced cut protection  
\*Arc Rating (ATPV) = 9.4 cal/cm2 Arc Category Level 2 per ASTM F2675-13

#### Performance Standards & Regulatory Compliance



#### Specifications

| BRAND   STYLE    | DESCRIPTION                                                                                                                                                       | Gauge | SIZE               | LENGTH                        | COATING COLOR | PACKAGE                                  |
|------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------|-------|--------------------|-------------------------------|---------------|------------------------------------------|
| ActivArm® 80-813 | <b>Finishing:</b> Palm Coated<br><b>Coating Material:</b> Neoprene Foam<br><b>Liner Material:</b> Fiber glass, Modacrylic, Aramid<br><b>Cuff Style:</b> Knitwrist | 13    | 6, 7, 8, 9, 10, 11 | 225-260 mm; 8.86-10.24 inches | Black         | • 12 pairs in a bag; 12 bags in a carton |

For additional information visit us at [www.ansell.com](http://www.ansell.com), or call us at

#### Europe, Middle East & Africa Region

Ansell Healthcare Europe NV  
Riverside Business Park  
Blvd International, 55  
1070 Brussels, Belgium  
T: +32 (0) 2 528 74 00  
F: +32 (0) 2 528 74 01

#### Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.  
Blvd. Bernardo Quintana No. 7001-C,  
Q7001 Torre II,  
Suites 1304, 1305 y 1306,  
Col. Centro Sur, c.p. 76079  
Queretaro, Qro. Mexico  
T: +52 442 248 1544 / 248 3133

#### North America Region

Ansell Healthcare Products LLC  
111 Wood Avenue South,  
Suite 900  
Iselin, NJ 08830, USA  
T: +1 800 800 0444  
F: +1 800 800 0445

#### Canada

Ansell Canada  
105 Lauder  
Cowansville, QC J2K 2K8  
Canada  
T: +1 800 363 8340  
F: +1 800 267 3551

#### Australia

Ansell Limited  
Level 3, 678 Victoria Street,  
Richmond, Vic, 3121  
Australia  
T: +61 1800 337 041  
F: +61 1800 803 578

#### Asia Pacific Region

Ansell Global Trading Center  
(Malaysia) Sdn Bhd  
Prima 6, Prima Avenue  
Block 3512, Jalan Teknokrat 6  
T: +603 8310 6688  
F: +603 8310 6699