

# HyFlex™

## 11-618

Palm coated glove for lightweight applications in dry and slightly oily environments



Multi Purpose Abrasion Protection



Light Duty

## Ultra-thin polyurethane gloves, with superb tactility and dexterity, for delicate handling

- **Enhanced dexterity:** HyFlex™ 11-618 multi-purpose gloves' light 18-gauge liner grants them excellent dexterity, for ease of use and minimal strain
- **Optimized tactility:** These HyFlex™ gloves' extra thin PU coating delivers optimal tactile sensitivity and a “second skin” feel, ideal for delicate handling
- **Improved durability:** Their PU coating not only enhances tactility but also ensures compliance with EN and ANSI/ISEA 105-2024 ABRASION LEVEL 3 standards
- **Considered aesthetics:** HyFlex™ 11-618 safety gloves' dark nylon liner masks dirt and stains, for long-lasting wear
- **Certified skin-friendliness:** Dermatest™ certification makes for dermatologically friendly personal protection



### Industries

- Automotive
- Metal fabrication

### Applications

- Picking, fastening components
- Assembling and mounting components
- Fastening components, parts

# HyFlex™

## 11-618

Palm coated glove for lightweight applications in dry and slightly oily environments

### Key Features

- ♦ **Light 18-gauge design:** Industrial gloves with optimal dexterity
- ♦ **Thin PU coating:** Tactile sensitivity with a “second skin” feel
- ♦ **Dark nylon liner:** Masks dirt and stains, for extended glove life

### Technologies



**Touchscreen Compatible**

### Performance Standards & Regulatory Compliance



ANSI/ISEA 105-2024



3121X

### Specifications

| BRAND   STYLE  | DESCRIPTION                                                                                                                            | Gauge | SIZE               | LENGTH                        | COATING COLOR | PACKAGE                        |
|----------------|----------------------------------------------------------------------------------------------------------------------------------------|-------|--------------------|-------------------------------|---------------|--------------------------------|
| HyFlex™ 11-618 | <b>Finishing:</b> Palm Coated<br><b>Coating Material:</b> Polyurethane<br><b>Liner Material:</b> Nylon<br><b>Cuff Style:</b> Knitwrist | 18    | 6, 7, 8, 9, 10, 11 | 195-245 mm / 7.63-9.96 inches | Black         | • 12 pairs/bag, 12 bags/carton |

For additional information visit us at [www.ansell.com](http://www.ansell.com), or call us at

#### Europe, Middle East & Africa Region

Ansell Healthcare Europe NV  
Riverside Business Park  
Blvd International, 55  
1070 Brussels, Belgium  
T: +32 (0) 2 528 74 00  
F: +32 (0) 2 528 74 01

#### North America Region

Ansell Healthcare Products LLC  
111 Wood Avenue South,  
Suite 900  
Iselin, NJ 08830, USA  
T: +1 800 800 0444  
F: +1 800 800 0445

#### Australia

Ansell Limited  
Level 3, 678 Victoria Street,  
Richmond, Vic, 3121  
Australia  
T: +61 1800 337 041  
F: +61 1800 803 578

#### Asia Pacific Region

Ansell Global Trading Center  
(Malaysia) Sdn Bhd  
Prima 6, Prima Avenue  
Block 3512, Jalan Teknokrat 6  
T: +603 8310 6688  
F: +603 8310 6699

#### Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.  
Blvd. Bernardo Quintana No. 7001-C,  
Q7001 Torre II,  
Suites 1304, 1305 y 1306,  
Col. Centro Sur, c.p. 76079  
Queretaro, Qro. Mexico  
T: +52 442 248 1544 / 248 3133

#### Canada

Ansell Canada  
105 Lauder  
Cowansville, QC J2K 2K8  
Canada  
T: +1 800 363 8340  
F: +1 800 267 3551

Ansell, ® and ™ are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending: [www.ansell.com/patentmarking](http://www.ansell.com/patentmarking) © 2025 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.