

HyFlex™

Sustainable medium-cut resistant glove



Cut



Light Duty

Delivers proven ISO C / ANSI A3 cut protection and long-lasting durability — helping reduce environmental impact without compromising safety or performance.

- **Advanced Yarn Innovation:** Delivers ISO C / ANSI A3 cut protection without the discomfort of metal or glass fibers. No poking, no breakage – just safe, comfortable protection in a lightweight 18-gauge design.
- **Lower Carbon Footprint:** Reduces carbon emissions by 44.9% compared to similar gloves*, as validated by LCA-certified testing. Made with over 50% recycled polyester recovered from post-consumer PET bottles**.
- **Highly Durable Coating:** DMF-free PU coating provides up to 4x more wear resistance than standard PU***, delaying liner exposure and extending glove life.
- **Certified Skin-Safe:** Free from DMF, silicone, and latex—common irritants in industrial gloves. Tested and certified by Dermatest™ and OEKO-TEX™.



*Based on size 9

**1 pair of 11-752 equals 1,21 standard plastic bottles (500ml, PET)

***Versus standard Ansell PU gloves with the same level of protection

Industries

- Automotive
- Machinery and Equipment
- Aerospace
- Manufacturing
- Infrastructure Maintenance

Applications

- Raw material handling
- Press shop operations
- Machining / Stamping / Cutting
- Metal Fabrication
- Hardware assembly
- Handling sharp metal or objects
- General handling
- Assembling metal parts and components
- Assembly of white goods

HyFlex™

Sustainable medium-cut resistant glove

Key Features

- ♦ **Advanced Yarn Innovation:** cut protection without metal or glass discomfort
- ♦ **Recycled Eco-Yarns:** over 50% PET content reduces carbon footprint by 44.9%*
- ♦ **DMF-Free PU Coating:** up to 4× higher wear resistance for longer glove life**

* Validated by LCA-certified testing based on size 9; 1 pair of 11-762 equals 1.55 standard plastic bottles (500ml, PET) ** Versus standard Ansell PU gloves with the same level of protection

Performance Standards & Regulatory Compliance



EN388: 2016



4X31C

EN 407



X1XXXX



2202040

Technologies



INTERCEPT™
Cut Resistance Technology



DMF free



Fibre glass free



METAL FREE

Specifications

BRAND STYLE	DESCRIPTION	Gauge	SIZE	LENGTH	COATING COLOR	PACKAGE
HyFlex™ 11-762	Finishing: Palm Coated, Thumbcrotch reinforcement Coating Material: DMF-Free Polyurethane Liner Material: Post-Consumer Recycled Polyester, Spandex, Elastic Cuff Style: Knitwrist	18	6, 7, 8, 9, 10, 11	209-268 mm / 8.22-10.55 inches	Black	• 12 pairs/paper band, 12 paper bands/carton

For additional information visit us at www.ansell.com, or call us at

Europe, Middle East & Africa Region

Ansell Healthcare Europe NV
Riverside Business Park
Blvd International, 55
1070 Brussels, Belgium
T: +32 (0) 2 528 74 00
F: +32 (0) 2 528 74 01

North America Region

Ansell Healthcare Products LLC
111 Wood Avenue South,
Suite 900
Iselin, NJ 08830, USA
T: +1 800 800 0444
F: +1 800 800 0445

Australia

Ansell Limited
Level 3, 678 Victoria Street,
Richmond, Vic, 3121
Australia
T: +61 1800 337 041
F: +61 1800 803 578

Asia Pacific Region

Ansell Global Trading Center
(Malaysia) Sdn Bhd
Prima 6, Prima Avenue
Block 3512, Jalan Teknokrat 6
T: +603 8310 6688
F: +603 8310 6699

Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.
Blvd. Bernardo Quintana No. 7001-C,
Q7001 Torre II,
Suites 1304, 1305 y 1306,
Col. Centro Sur, c.p. 76079
Queretaro, Qro. Mexico
T: +52 442 248 1544 / 248 3133

Canada

Ansell Canada
105 Lauder
Cowansville, QC J2K 2K8
Canada
T: +1 800 363 8340
F: +1 800 267 3551

Ansell, ® and ™ are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending: www.ansell.com/patentmarking © 2025 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.

Ansell