

## Comfortable gloves offering tactility and protection across numerous applications

- **Elevated comfort:** Ansell MICROFLEX® 92-134 Versatility disposable safety gloves are made of a soft nitrile formulation, which provides a highly comfortable fit and feel while protecting hands
- **Heightened tactility:** These nitrile disposable gloves' lightweight construction provides augmented tactile sensitivity and fine motor control
- **Optimized grip:** These MICROFLEX® gloves are textured on the fingertips to ensure a stronger grip for the safer handling of tools and materials
- **Genuine versatility:** Designed for a broad range of applications, these gloves reinforce hand protection across a wide range of industries



### Industries

- Healthcare
- Automotive
- Food Processing
- Janitorial / Sanitation
- Manufacturing
- Life Sciences

### Recommended For

- Catering/Meal preparation
- Picking parts and accessories
- Food processing and handling
- Light assembly tasks
- Lab work, blending, compounding, filling, cleaning
- Preparing pharmaceutical products
- Laboratory analysis
- Standard patient examinations
- Disposal of waste (trash, biohazard and linens)

# TECHNICAL DATA SHEET

|                        | Product Information                                                                                                                                                                                                                                                                                                                                    |
|------------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Material               | Nitrile                                                                                                                                                                                                                                                                                                                                                |
| External Glove Surface | Textured Fingers                                                                                                                                                                                                                                                                                                                                       |
| Audit Standards        | ISO 13485, ISO 9001                                                                                                                                                                                                                                                                                                                                    |
| Product Certification  | Medical Device Regulation (EU) 2017/745 Class I, Personal Protective Equipment Regulation (EU) 2016/425 Category III risks, KR M ISO 11193, EN ISO 21420:2020, EN ISO 374-1:2016 Type B JKT, EN ISO 374-5:2016 Virus, ISO 18889:2019, EN 455 1-4, EU Food Contact Approved, ASTM D6319, ISO 13485, ISO 9001, ISO 10993-5, 10, 23, ISO 16604, ISO 11737 |
| Packaging Overview     | 100 gloves per dispenser, 10 dispensers per case, 1000 gloves per case                                                                                                                                                                                                                                                                                 |
| Storage Instructions   | Keep out of direct sunlight; store in a cool and dry place. Keep away from sources of ozone or ignition.                                                                                                                                                                                                                                               |
| Product Segmentation   | Standard Thin                                                                                                                                                                                                                                                                                                                                          |
| Antistatic             | No                                                                                                                                                                                                                                                                                                                                                     |
| Silicone Free          | No                                                                                                                                                                                                                                                                                                                                                     |

## PHYSICAL PROPERTIES

|                                         | Typical Values |             | Testing Method   |
|-----------------------------------------|----------------|-------------|------------------|
| Length (mm/inches)                      | 240 / 9.5      |             | ASTM D6319       |
| Freedom from Holes (Inspection level I) | 1.5 AQL        |             | ASTM D5151       |
| Finger Thickness (mm/mils)              | 0.11 / 4.3     |             | ASTM D6319       |
|                                         | BEFORE AGING   | AFTER AGING |                  |
| Ultimate Tensile Strength (MPa)         | ≥ 14           | ≥ 14        | EN 455-2         |
| Elongation at Break (%)                 | ≥ 500          | ≥ 400       | ASTM D412 & D573 |
| Force at break (N)                      | ≥ 6            | ≥ 6         |                  |

ORDERING INFORMATION

| Size         | XS (5.5 - 6) | S (6.5 - 7) | M (7.5 - 8) | L (8.5 - 9) |
|--------------|--------------|-------------|-------------|-------------|
| Product Code | 92134060     | 92134070    | 92134080    | 92134090    |

Performance Standards and Regulatory Compliance

EN ISO 374-1:2016  
Type B

  
J K T

EN ISO 374-5

  
VIRUS





ISO

ISO 10993-10

ISO

ISO 10993-23

ISO

ISO 13485

ISO

ISO 16604

  
G1

ISO 18889

ISO

ISO 9001

MD

For additional information visit us at [www.ansell.com](http://www.ansell.com), or call us at

**Europe, Middle East & Africa Region**  
Ansell Healthcare Europe NV  
T: +32 (0) 2 528 74 00  
F: +32 (0) 2 528 74 01

**Asia Pacific Region**  
MY: +603 8310 6688  
apac.medical@ansell.com  
CN: +86 21 38275000  
infochina@ansell.com  
JP: +813 5549 8151  
info.medical.jp@ansell.com

**North America Region**  
Ansell Healthcare Products LLC  
T: +1 800 800 0444  
F: +1 800 800 0445

**Latin America & Caribbean Region**  
BR: +55 (11) 3356-3100  
latam.medical@ansell.com  
MX: +52 442 296 2050  
latam.medical@ansell.com  
CO: +57 1 288 3247  
latam.medical@ansell.com

**Australia**  
Ansell Limited  
T: +61 1800 337 041  
F: +61 1800 803 578

**Russia**  
Ansell PYC  
Ten. +7 495 258 13 16

Ansell, ® and ™ are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending: [www.ansell.com/patentmarking](http://www.ansell.com/patentmarking) © 2025 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.

