

# ACTIVARMR™

## Electrical Insulating Gloves Class 00 – RIG0014B

Comfortable electrical protection gloves,  
combining safety, durability and flexibility

Previously known as: E015B



Electrical



Light Duty

## Durable, form-fitting electrical safety gloves, assuredly protecting wearers\*

- **Improved durability and flexibility:** ActivArmr™ Electrical Insulating Gloves Class 00 – RIG0014B are made of durable, flexible latex, using an eco-conscious dipping process
- **Advanced ergonomics:** These insulated gloves' hand-at-rest design and non-splayed fingers limit hand fatigue
- **Elevated comfort:** Their spacious flared cuff enhances ventilation and makes room for clothing
- **Increased practicality:** These electrical protection gloves' smooth, case-hardened finish makes for easy donning and doffing
- **Specialized defenses:** They are arc flash certified (APC 1 in combination with 96-002 leather protectors) and tolerate a touch voltage maximum of AC 500 V (DC 750 V)
- **Certified protection:** These electrical insulated gloves meet relevant CSA, NFPA and OSHA standards, as well as EN standards for acid, ozone and low temperature resistance\*  
\*Category A, Z and C respectively



ARC FLASH  
RESISTANT

### Industries

- Automotive
- Construction
- Energy

### Applications

- Applications with risk of touch voltage
- Electrical Contractors
- Hybrid engine manufacturing and repair
- Maintenance Repairs and Operations in all industrial environments (MRO)
- Mass Transit Repair and Maintenance
- Power maintenance, repair & transmission
- Telecom repair near electrical wires

# ACTIVARMR™

## Electrical Insulating Gloves Class 00 – RIG0014B


Comfortable electrical protection gloves,  
combining safety, durability and flexibility

Previously known as: E015B

### Key Features

- ◊ **Natural rubber latex formulation:** Assured flexibility and durability
- ◊ **Ergonomic design:** Better dexterity, less hand fatigue
- ◊ **Generous flared cuff:** Enhanced room for clothing and ventilation  
\*Arc flash certified as per IEC 614821-2:2014 and ASTM F2675:2021 standards

### Performance Standards & Regulatory Compliance



### Specifications

BRAND   STYLE	DESCRIPTION	SIZE	LENGTH	COATING COLOR	PACKAGE
ActivArmr Electrical Insulating Gloves Class 00 – RIG0014B	<b>Coating Material:</b> Natural Rubber Latex <b>Cuff Style:</b> Straight Cuff with rolled beaded edge	7, 8, 8.5, 9, 9.5, 10, 10.5, 11, 12	360 / 14.17	Black	● 1 pair/pack, 10 pairs/carton

For additional information visit us at [www.ansell.com](http://www.ansell.com), or call us at

**Europe, Middle East & Africa Region**  
Ansell Healthcare Europe NV  
Riverside Business Park  
Blvd International, 55  
1070 Brussels, Belgium  
T: +32 (0) 2 528 74 00  
F: +32 (0) 2 528 74 01

**North America Region**  
Ansell Healthcare Products LLC  
111 Wood Avenue South,  
Suite 900  
Iselin, NJ 08830, USA  
T: +1 800 800 0444  
F: +1 800 800 0445

**Australia**  
Ansell Limited  
Level 3,678 Victoria Street,  
Richmond, Vic, 3121  
Australia  
T: +61 1800 337 041  
F: +61 1800 803 578

**Asia Pacific Region**  
Ansell Global Trading Center  
(Malaysia) Sdn Bhd  
Prima 6, Prima Avenue  
Block 3512, Jalan Teknokrat 6  
T: +603 8310 6688  
F: +603 8310 6699

**Latin America & Caribbean Region**  
Ansell Commercial Mexico S.A. de C.V.  
Blvd. Bernardo Quintana No. 7001-C,  
Q7001 Torre II,  
Suites 1304, 1305 y 1306,  
Col. Centro Sur, c.p. 76079  
Queretaro, Qro, Mexico  
T: +52 442 248 1544 / 248 3133

**Canada**  
Ansell Canada  
105 Lauder  
Cowansville, QC J2K 2K8  
Canada  
T: +1 800 363 8340  
F: +1 800 267 3551

Ansell, ® and ™ are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending: [www.ansell.com/patentmarking](http://www.ansell.com/patentmarking) © 2025 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.

The Ansell logo consists of the word 'Ansell' in a bold, blue, sans-serif font. A green swoosh underline is positioned beneath the letters 'n' and 's'.