



Cut



Light Duty

## Our lightest ANSI/ISEA105-2024 CUT A3 and EN ISO C glove\* offers 2x greater cut resistance\*\*

- **Enhanced comfort:** The HyFlex® 11-561 featuring an ultra-lightweight design, is 20% lighter while meeting ANSI/ISEA 105-2024 CUT A3 and EN ISO C standards\*
- **Heightened defenses:** 2 times greater cut resistance\*\* using Next Generation single HPPE yarn developed with INTERCEPT™ Cut Resistance Technology for reliable hand protection
- **Increased durability for extended use:** Improved FORTIX™ Technology delivers up to 20% more abrasion resistance for longer lasting handling in abrasive conditions\*\*\*
- **Excellent grip:** HyFlex 11-561's palm-dipped coating improves grip, while a reinforced thumb crotch defends against rapid wear
- **Certified harm-free:** Dermatest® and Oeko-Tex® certification ensures these PPE gloves are skin-friendly and free of harmful substances
- **Touchscreen compatible:** Allows the wearer to work with multiple touchscreen devices while keeping gloves on

\* Versus standard ANSI/ISEA 105-2024 CUT A4 and EN ISO D rated gloves

\*\* Versus similar gloves made of standard HPPE yarn

\*\*\* Versus previous technology version



### Industries

- Automotive
- Energy
- Automotive Aftermarket

### Applications

- Handling metal sheets & panels
- Handling parts with sharp, rough edges
- Final assembly
- Handling materials with sharp or rough edges
- Assembly & inspection of components
- Applying finish to materials, products
- Compatible with consumer and industrial touchscreens

# HyFlex®

ADVANCED MECHANICAL PROTECTION

## 11-561

20% lighter design\* with powerful cut protection

### Key Features

- ♦ **Ultra-lightweight design:** 20% lighter\* for unparalleled comfort and dexterity
- ♦ **ANSI/ISEA 105-2024 CUT A3 and EN ISO C protection:** Provides 2x greater cut resistance
- ♦ **Improved FORTIX™ Technology:** up to 20% greater durability\*\*\*

\* Versus standard ANSI/ISEA 105-2024 CUT A3 and EN ISO C gloves

\*\* Versus similar gloves made of standard HPPE yarn

\*\*\* Versus previous technology version

### Technologies



DMF free



Fibre glass free



**FORTIX™**

Abrasion Resistance Technology



**INTERCEPT™**

Cut Resistance Technology



### Performance Standards & Regulatory Compliance



4X42C

ANSI/ISEA 105-2024



EN388: 2016



4X42C



X1XXXX



STANDARD 100

1408033  
Centexbel

### Specifications

BRAND   STYLE	DESCRIPTION	Gauge	SIZE	LENGTH	COATING COLOR	PACKAGE
HyFlex® 11-561	<b>Finishing:</b> Palm Coated, Thumbcrotch reinforcement <b>Coating Material:</b> Nitrile <b>Liner Material:</b> INTERCEPT™ reinforced HPPE yarn <b>Cuff Style:</b> Knitwrist	15	5, 6, 7, 8, 9, 10, 11, 12	210-285 mm / 8.27-11.22 inches	Grey	• 12 pairs/bag, 12 bags/carton

For additional information visit us at [www.ansell.com](http://www.ansell.com), or call us at

#### Europe, Middle East & Africa Region

Ansell Healthcare Europe NV  
Riverside Business Park  
Blvd International, 55  
1070 Brussels, Belgium  
T: +32 (0) 2 528 74 00  
F: +32 (0) 2 528 74 01

#### Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.  
Blvd. Bernardo Quintana No. 7001-C,  
Q7001 Torre II,  
Suites 1304, 1305 y 1306,  
Col. Centro Sur, c.p. 76079  
Queretaro, Qro. Mexico  
T: +52 442 248 1544 / 248 3133

#### North America Region

Ansell Healthcare Products LLC  
111 Wood Avenue South,  
Suite 900  
Iselin, NJ 08830, USA  
T: +1 800 800 0444  
F: +1 800 800 0445

#### Canada

Ansell Canada  
105 Lauder  
Cowansville, QC J2K 2K8  
Canada  
T: +1 800 363 8340  
F: +1 800 267 3551

#### Australia

Ansell Limited  
Level 3, 678 Victoria Street,  
Richmond, Vic, 3121  
Australia  
T: +61 1800 337 041  
F: +61 1800 803 578

#### Asia Pacific Region

Ansell Global Trading Center  
(Malaysia) Sdn Bhd  
Prima 6, Prima Avenue  
Block 3512, Jalan Teknokrat 6  
T: +603 8310 6688  
F: +603 8310 6699