



Cut



Oil

Ergonomic Protection



Light Duty

Ultralight, three quarter-coated cut-resistant and oil-repellent work gloves

- **Specialized protection:** Meets ANSI/ISEA 105-2024 CUT A2 and EN ISO B standards, with RIPEL™ Liquid Repellence Technology to stop oil and liquid contact with the skin
- **Targeted defenses:** The HyFlex™ 11-937's reinforced thumb crotch delivers 12x more resilience in the thumb area
- **Improved durability:** FORTIX™ Abrasion Resistance foam coating makes these HyFlex™ gloves 12x more abrasion-resistant
- **Lightened feel:** HyFlex™ 11-937 PPE gloves' ultralight 18-gauge design and ERGOFORM™ Technology deliver superb dexterity
- **Enhanced grip:** ANSELL GRIP™ coating treatment reduces the force required to maintain grip, ensuring workplace safety
- **Elevated comfort:** ZONZ™ Comfort Fit's knitting and stitch design lowers hand fatigue, for maneuverable, form-fitting industrial gloves



Industries

- Automotive
- Automotive Aftermarket
- Machinery and Equipment
- Metal fabrication
- Agriculture
- Infrastructure Maintenance
- Chemical

Applications

- Inspection, selecting, checking parts
- Assembly & inspection of components
- Picking, fastening components
- Chassis assembly, body trimming
- Adjusting parts, systems
- Delivery of parts to production line
- Equipment repair & maintenance
- Engine transmission and repair
- Oil, fluids and filter change
- Inspection (picking, checking and marking)
- Feeding the press and removing spare parts from it
- Fastening components, parts
- Adjusting panels parts components
- Press shop operations

Key Features

- ◊ **RIPEL™ Liquid Repellence:** Defense against oil and chemicals
- ◊ **Reinforced thumb crotch:** 12x greater durability around the thumb*
- ◊ **Ultralight 18-gauge design:** All-day comfort and dexterity
*compared to competitor gloves lacking this feature

Technologies



DMF free



Dyneema®



Fibre glass free



Touchscreen Compatible



Performance Standards & Regulatory Compliance

ANSI/ISEA 105-2024



CE 0493



EN388: 2016



4X42B



ISO 18889



4419CIT

Specifications

BRAND STYLE	DESCRIPTION	Gauge	SIZE	LENGTH	COATING COLOR	PACKAGE
HyFlex™ 11-937	Finishing: 3/4 Coated Coating Material: Foam Nitrile Liner Material: Dyneema® Diamond Technology Cuff Style: Knitwrist	18	6, 7, 8, 9, 10, 11	212-261 mm / 8.3-10.3 inches	Grey and Black	• 12 pairs/bag, 12 bags/carton

For additional information visit us at www.ansell.com, or call us at

Europe, Middle East & Africa Region

Ansell Healthcare Europe NV
Riverside Business Park
Blvd International, 55
1070 Brussels, Belgium
T: +32 (0) 2 528 74 00
F: +32 (0) 2 528 74 01

Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.
Blvd. Bernardo Quintana No. 7001-C,
Q7001 Torre II,
Suites 1304, 1305 y 1306,
Col. Centro Sur, c.p. 76079
Queretaro, Qro. Mexico
T: +52 442 248 1544 / 248 3133

North America Region

Ansell Healthcare Products LLC
111 Wood Avenue South,
Suite 900
Iselin, NJ 08830, USA
T: +1 800 800 0444
F: +1 800 800 0445

Canada

Ansell Canada
105 Lauder
Cowansville, QC J2K 2K8
Canada
T: +1 800 363 8340
F: +1 800 267 3551

Australia

Ansell Limited
Level 3, 678 Victoria Street,
Richmond, Vic, 3121
Australia
T: +61 1800 337 041
F: +61 1800 803 578

Asia Pacific Region

Ansell Global Trading Center
(Malaysia) Sdn Bhd
Prima 6, Prima Avenue
Block 3512, Jalan Teknokrat 6
T: +603 8310 6688
F: +603 8310 6699