

## Ergonomically designed to reduce hand fatigue

- **Reduced allergy risk:** MICROFLEX™ 93-833 gloves are manufactured without accelerators for low dermatitis potential. These gloves prevent instances of Type I latex allergies and Type IV chemical allergic reactions
- **Extra durability:** stronger formulation to protect against rips and tears while keeping the same tactile sensitivity
- **Enhanced comfort:** softer formulation for a lightweight, softer skin feel
- **ERGOFORM™ Technology:** designed with proprietary ergonomic design technology to support musculoskeletal health and increase worker productivity
- **Reduced waste:** Gloves are smartly packaged, with 250 gloves per box and easy, single glove dispensing to reduce waste
- **Strong barrier integrity:** With a low 0.65 AQL, these gloves offer advanced barrier integrity



### Industries

- Automotive Aftermarket
- Food Processing
- Life Sciences
- Healthcare
- Fire and Rescue
- Dental
- Automotive

### Recommended For

- General Purpose Auto Aftermarket
- All food processing, applications that have food contact
- Sample taking and processing
- Protection from Type I latex allergy in HCW's or patients
- Protection from Type IV chemical allergies in HCW's or patients
- Assembly of parts
- Enhanced tactile sensitivity and dexterity, especially for delicate procedures
- Extra comfort during long, sustained procedures
- Standard patient examinations

## TECHNICAL DATA SHEET

|                        | Product Information                                                                                                                                                                                                                                                                                                                                                                                                                                     |
|------------------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Material               | Nitrile                                                                                                                                                                                                                                                                                                                                                                                                                                                 |
| External Glove Surface | Textured Fingers                                                                                                                                                                                                                                                                                                                                                                                                                                        |
| Audit Standards        | ISO 13485, ISO 9001                                                                                                                                                                                                                                                                                                                                                                                                                                     |
| Product Certification  | Medical Device Regulation (EU) 2017/745 Class I, Personal Protective Equipment Regulation (EU) 2016/425 Category III risks, ASTM D6319, CE 0493, EC 1935/2004, EC 2023/2006, EN 1149-1/2/3, EN 16523-1, EN ISO 374-5:2016 Virus, EN ISO 21420:2020, EN ISO 374-1:2016 Type B KPT, EN 421:2010, EN 455 1-4, FDA21 CFR 177-2600-US Food Contact Approved, EU Food Contact Approved, ISO 13485, ISO 9001, PMDA Notification Number: 13B3X10307AH0001, UKCA |
| Packaging Overview     | 250 gloves per dispenser<br>10 dispensers per case<br>2500 gloves per case<br>XL: 230 gloves per dispenser                                                                                                                                                                                                                                                                                                                                              |
| Storage Instructions   | Keep out of direct sunlight; store in a cool and dry place. Keep away from sources of ozone or ignition.                                                                                                                                                                                                                                                                                                                                                |
| Country Of Origin      | Malaysia                                                                                                                                                                                                                                                                                                                                                                                                                                                |
| Product Segmentation   | High Touch                                                                                                                                                                                                                                                                                                                                                                                                                                              |
| Antistatic             | Yes EN1149                                                                                                                                                                                                                                                                                                                                                                                                                                              |
| Silicone Free          | No                                                                                                                                                                                                                                                                                                                                                                                                                                                      |


## PHYSICAL PROPERTIES

|                                         | Typical Values      |                    | Testing Method      |
|-----------------------------------------|---------------------|--------------------|---------------------|
| Length (mm/inches)                      | 240 / 9.45          |                    | ASTM D3767,EN 420   |
| Freedom from Holes (Inspection level I) | 0.65 AQL            |                    | ASTM D5151,EN 455-1 |
| Palm Thickness (mm/mils)                | 0.07 / 2.8          |                    | ASTM D3767,EN 420   |
| Finger Thickness (mm/mils)              | 0.11 / 4.3          |                    | ASTM D3767,EN 420   |
|                                         | <b>BEFORE AGING</b> | <b>AFTER AGING</b> |                     |
| Elongation at Break (%)                 | ≥ 500               | ≥ 400              | ASTM D412           |
| Force at break (N)                      | ≥ 6                 | ≥ 6                | EN 455-2            |

ORDERING INFORMATION

| Size         | XS (5.5 – 6) | S (6.5 – 7) | M (7.5 – 8) | L (8.5 – 9) | XL (9.5 – 10) |
|--------------|--------------|-------------|-------------|-------------|---------------|
| Product Code | 93833060     | 93833070    | 93833080    | 93833090    | 93833100      |

Performance Standards and Regulatory Compliance



For additional information visit us at [www.ansell.com](http://www.ansell.com), or call us at

**Europe, Middle East & Africa Region**  
Ansell Healthcare Europe NV  
T: +32 (0) 2 528 74 00  
F: +32 (0) 2 528 74 01  
**Asia Pacific Region**  
MY: +603 8310 6688  
apac.medical@ansell.com  
CN: +86 21 38275000  
infochina@ansell.com  
JP: +813 5549 8151  
info.medical.jp@ansell.com

**North America Region**  
Ansell Healthcare Products LLC  
T: +1 800 800 0444  
F: +1 800 800 0445  
**Latin America & Caribbean Region**  
BR: +55 (11) 3356-3100  
latam.medical@ansell.com  
MX: +52 442 296 2050  
latam.medical@ansell.com  
CO: +57 1 288 3247  
latam.medical@ansell.com

**Australia**  
Ansell Limited  
T: +61 1800 337 041  
F: +61 1800 803 578  
**Russia**  
Ansell PYC  
Ten. +7 495 258 13 16



Ansell, ® and ™ are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending: [www.ansell.com/patentmarking](http://www.ansell.com/patentmarking) © 2025 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.

