

Latex disposable gloves with textured fingers, designed for Class 100 (ISO 5) environments

- **Elevated comfort:** MICROFLEX™ CE5-512 cleanroom gloves are made using a soft latex formulation, offering an ideal blend of comfort and dexterity
- **Enhanced grip:** These disposable latex gloves are also designed with textured fingers, for solid grip performance in various conditions
- **Assured product integrity:** As these MICROFLEX™ gloves are free of silicone, they pose a lesser risk to product and component integrity



KEY FEATURES & BENEFITS

- ◊ **Soft latex formulation:** A balance of comfort and dexterity
- ◊ **Textured fingers:** Enhanced grip performance
- ◊ **Silicone-free design:** Assured product protection

Industries

- Pharmaceutical Manufacturing
- Biotechnology Manufacturing
- Electronics manufacturing

Recommended For

- Clean room cleaning and preparing
- Spill or leakage cleanup
- Transferring liquids and solids
- Weighing and dispensing of solid and liquid raw materials
- Loading centrifuges and chromatography columns
- Blending, compounding solids and liquids
- Assembly of parts



TECHNICAL DATA SHEET

	Product Information
Material	Natural Rubber Latex
Color	Natural
Shape	Ambidextrous
Cuff	Beaded
Manufacturing/QMS Audit Standards	ISO 9001:2015
Packaging	100 gloves per inner polybag, 1 inner polybag per outer bag, 10 outer bags per lined carton
Storage	Keep out of direct sunlight; store in a cool and dry place. Keep away from sources of ozone or ignition.
Available sizes	XS (5.5 - 6), S (6.5 - 7), M (7.5 - 8), L (8.5 - 9), XL (9.5 - 10)
Powder Content	Powder-Free
External Glove Surface	Textured Fingers
Internal Glove Surface	Powder-Free
Sterilization Method	Not Applicable
Cleanroom Class	Class 100/ISO 5
Shelf Life	3 Years
Tested for use with Chemotherapy Drugs	No
Protein Level	50 µg/g or less of total extractable protein
Anti-static	No

MICRO $\oplus$ FLEX™

CE5-512

Non-sterile Disposable Latex Cleanroom Glove

Physical Properties		Testing Method
Typical Length (mm/in)	300 / 12	EN 420/ASTM D3767
Freedom from Holes	1.5 AQL	EN 455-1,ASTM D5151-06 (2011)
Typical Particle Count $\geq 0.5\mu\text{m}$ (counts / cm^2)	< 2,000 particles / cm^2	IEST-RP-CC005.4

ORDERING INFORMATION

SIZE	XS (5.5 - 6)	S (6.5 - 7)	M (7.5 - 8)	L (8.5 - 9)	XL (9.5 - 10)
REORDER NO.	CE5-512-XS	CE5-512-S	CE5-512-M	CE5-512-L	CE5-512-XL

PERFORMANCE STANDARDS AND REGULATORY COMPLIANCE

For additional information visit us at www.ansell.com, or call us at

Europe, Middle East & Africa Region

Ansell Healthcare Europe NV
T: +32 (0) 2 528 74 00
F: +32 (0) 2 528 74 01

Asia Pacific Region

Ansell Global Trading Center
T: +603 8310 6688
F: +603 8310 6699

North America Region

Ansell Healthcare Products LLC
US T: +1 800 800 0444
US F: +1 800 800 0445
CA T: +1-800-363-8340

Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.
T: +52 442 248 1544 / 248 3133

Australia

Ansell Limited
T: +61 1800 337 041
F: +61 1800 803 578

UK

Ansell Nitritex
T: +44 1638 663338
F: +44 1638 668890

Ansell, ® and ™ are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending:
www.ansell.com/patentmarking © 2025 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.

