

Chemical-resistant disposable gloves that offer tough chemical resistance and superior comfort

- **Three-layer design:** Three layers ensure superior protection against harsh chemicals
- **Thin mil design:** Designed to be thinner than standard reusable chemical-resistant gloves (7.8 mil) for protection that allows for better tactility when handling small objects and tools
- **Elevated comfort:** Soft material and ergonomic design offer outstanding fit, feel and flexibility
- **Assured quality:** Their low AQL (0.65) means minimal pinhole defect risks
- **High standards:** Meets EN 374 Type A certified in Europe and KOSHA certified in Korea
- **Retail pack 93-260RP:** Available in convenient packaging of 6 gloves, size specific



Industries

- Aerospace
- Automotive
- Automotive Aftermarket
- Life Sciences
- Chemical
- Agriculture
- Machinery and Equipment
- Metal fabrication
- Utilities
- Warehousing

Recommended For

- Inspection, selecting, checking parts
- Assembly and inspection of components
- Equipment repair and maintenance
- Production line support and maintenance
- General Purpose Auto Aftermarket
- Oil, fluids and filter change
- Blending, compounding solids and liquids
- Sample taking and processing
- Transferring liquids and solids between vessels and tanks and process equipment

TECHNICAL DATA SHEET

	Product Information
Material	Nitrile, Neoprene (Polychloroprene)
External Glove Surface	Textured Fingers
Audit Standards	ISO 9001
Product Certification	Personal Protective Equipment Regulation (EU) 2016/425 Category III risks, EN 388:2016 2000X, CE 0493, EN 421:2010, EN ISO 21420:2020, EN ISO 374-1:2016 Type A JKLOPST, EN ISO 374-5:2016 Virus, FDA21 CFR 177-2600-US Food Contact Approved, ISO 18889:2019, ISO 9001, DOSH-SIRIM certified, Kosha certified, UKCA
Packaging Overview	50 gloves per dispenser 10 dispensers per case 500 gloves per case Retail Pack: 6 gloves per pack; 50 packs per case; 300 gloves per case
Storage Instructions	Keep out of direct sunlight; store in a cool and dry place. Keep away from sources of ozone or ignition.
Country Of Origin	Sri Lanka
Product Segmentation	High Risk
Antistatic	Yes EN1149
Fentanyl Tested	Yes
Silicone Free	Yes

PHYSICAL PROPERTIES

	Typical Values		Testing Method
Length (mm/inches)	≥ 285 / 11.2		ASTM D3767,EN 420
Freedom from Holes (Inspection level I)	0.65 AQL		ASTM D5151,EN 455-1
Palm Thickness (mm/mils)	0.198/ 7.9		ASTM D3767,EN 420
Finger Thickness (mm/mils)	0.20/ 7.9		ASTM D3767,EN 420
	BEFORE AGING	AFTER AGING	
Ultimate Tensile Strength (MPa)	≥ 14	≥ 14	ASTM D412 & D573
Elongation at Break (%)	≥ 500	≥ 400	ASTM D412
Force at break (N)	≥ 6	≥ 6	EN 455-2

ORDERING INFORMATION

Size	XS (5.5 - 6)	S (6.5 - 7)	M (7.5 - 8)	L (8.5 - 9)	XL (9.5 - 10)	XXL (10.5 - 11)	M (7.5 - 8)	L (8.5 - 9)	XL (9.5 - 10)	XXL (10.5 - 11)
Product Code	932600060	932600070	932600080	932600090	93260100	93260110	93260RP080	93260RP090	93260RP100	93260RP110
Retail Pack Catalog No			93260RP080	93260RP090	93260RP100		93260RP080	93260RP090	93260RP100	

Performance Standards and Regulatory Compliance



Ansell, ® and ™ are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending:
www.ansell.com/patentmarking © 2025 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.

