

# Chemical-resistant disposable gloves that offer tough chemical resistance and superior comfort

- **Three-layer design:** Three layers ensure superior protection against harsh chemicals
- **Thin mil design:** Designed to be thinner than standard reusable chemical-resistant gloves (7.8 mil) for protection that allows for better tactility when handling small objects and tools
- **Elevated comfort:** Soft material and ergonomic design offer outstanding fit, feel and flexibility
- **Assured quality:** Their low AQL (0.65) means minimal pinhole defect risks
- **High standards:** Meets EN 374 Type A certified in Europe and KOSHA certified in Korea
- **Retail pack 93-260RP:** Available in convenient packaging of 6 gloves, size specific



## Industries

- Aerospace
- Automotive
- Automotive Aftermarket
- Life Sciences
- Chemical
- Agriculture
- Machinery and Equipment
- Metal fabrication
- Utilities
- Warehousing

## Recommended For

- Inspection, selecting, checking parts
- Assembly and inspection of components
- Equipment repair and maintenance
- Production line support and maintenance
- General Purpose Auto Aftermarket
- Oil, fluids and filter change
- Blending, compounding solids and liquids
- Sample taking and processing
- Transferring liquids and solids between vessels and tanks and process equipment

## TECHNICAL DATA SHEET

	Product Information
Material	Nitrile, Neoprene (Polychloroprene)
External Glove Surface	Textured Fingers
Audit Standards	ISO 9001
Product Certification	Personal Protective Equipment Regulation (EU) 2016/425 Category III risks, EN 388:2016 2000X, CE 0493, EN 421:2010, EN ISO 21420:2020, EN ISO 374-1:2016 Type A JKLOPST, EN ISO 374-5:2016 Virus, FDA21 CFR 177-2600-US Food Contact Approved, ISO 18889:2019, ISO 9001, DOSH-SIRIM certified, Kosha certified, UKCA
Packaging Overview	50 gloves per dispenser 10 dispensers per case 500 gloves per case  <b>Retail Pack:</b> 6 gloves per pack; 50 packs per case; 300 gloves per case
Storage Instructions	Keep out of direct sunlight; store in a cool and dry place. Keep away from sources of ozone or ignition.
Country Of Origin	Sri Lanka
Product Segmentation	High Risk
Antistatic	Yes EN1149
Fentanyl Tested	Yes
Silicone Free	Yes

## PHYSICAL PROPERTIES

	Typical Values		Testing Method
Length (mm/inches)	≥ 285 / 11.2		ASTM D3767,EN 420
Freedom from Holes (Inspection level I)	0.65 AQL		ASTM D5151,EN 455-1
Palm Thickness (mm/mils)	0.198/ 7.9		ASTM D3767,EN 420
Finger Thickness (mm/mils)	0.20/ 7.9		ASTM D3767,EN 420
	BEFORE AGING	AFTER AGING	
Ultimate Tensile Strength (MPa)	≥ 14	≥ 14	ASTM D412 & D573
Elongation at Break (%)	≥ 500	≥ 400	ASTM D412
Force at break (N)	≥ 6	≥ 6	EN 455-2

## ORDERING INFORMATION

Size	XS (5.5 - 6)	S (6.5 - 7)	M (7.5 - 8)	L (8.5 - 9)	XL (9.5 - 10)	XXL (10.5 - 11)	M (7.5 - 8)	L (8.5 - 9)	XL (9.5 - 10)	XXL (10.5 - 11)
Product Code	93260060	93260070	93260080	93260090	93260100	93260110	93260RP080	93260RP090	93260RP100	93260RP110
Retail Pack Catalog No			93260RP080	93260RP090	93260RP100		93260RP080	93260RP090	93260RP100	

## Performance Standards and Regulatory Compliance



Ansell, ® and ™ are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending:  
www.ansell.com/patentmarking © 2025 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.

