

## Cleanroom Overshoes

BioClean ESD Cleanroom Overshoes have non-marking conductive tape providing dissipative properties when worn as instructed.

### KEY FEATURES & BENEFITS

- ◊ Non-marking conductive tape
- ◊ ESD properties



### Industries

- Controlled and Critical Environments
- Production and Manufacturing



## ESD Cleanroom Overshoes

### TECHNICAL DATA SHEET

|                                   | Product Information                                                                                                                                                                                                                                                                                                                                       |
|-----------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Material                          | Polypropylene Spunbond + Nylon + Polyester                                                                                                                                                                                                                                                                                                                |
| Color                             | White, Blue                                                                                                                                                                                                                                                                                                                                               |
| Manufacturing/QMS Audit Standards | Manufacturing QMS Audit Standards ISO 9001                                                                                                                                                                                                                                                                                                                |
| Packaging                         | 100 pieces per sealed inner PE bag; one inner bag per sealed outer PE bag; 10 outer bags per lined carton (1000 pieces)<br><br>Please Note: When donning the ESD overshoes ensure that the loose black tape is located at the back/heel of the foot and is tucked securely inside the users sock making sure the tape is in direct contact with the skin. |
| Storage                           | Store in a dry, cool place (<40°C) away from direct sunlight and fluorescent light.                                                                                                                                                                                                                                                                       |
| Available sizes                   | 16" (40cm)                                                                                                                                                                                                                                                                                                                                                |
| Shelf Life                        | 5 years                                                                                                                                                                                                                                                                                                                                                   |



## ESD Cleanroom Overshoes

### ORDERING INFORMATION

| SIZE        | 10        |
|-------------|-----------|
| REORDER NO. | code test |

### PERFORMANCE STANDARDS AND REGULATORY COMPLIANCE

For additional information visit us at [www.ansell.com](http://www.ansell.com), or call us at

#### Europe, Middle East & Africa Region

Ansell Healthcare Europe NV  
T: +32 (0) 2 528 74 00  
F: +32 (0) 2 528 74 01

#### Asia Pacific Region

Ansell Global Trading Center  
T: +603 8310 6688  
F: +603 8310 6699

#### North America Region

Ansell Healthcare Products LLC  
US T: +1 800 800 0444  
US F: +1 800 800 0445  
CA T: +1-800-363-8340

#### Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.  
T: +52 442 248 1544 / 248 3133

#### Australia

Ansell Limited  
T: +61 1800 337 041  
F: +61 1800 803 578

#### UK

Ansell Nitritex  
T: +44 1638 663338  
F: +44 1638 668890

Ansell, ® and ™ are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending:  
[www.ansell.com/patentmarking](http://www.ansell.com/patentmarking) © 2025 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.

