



Cut

Abrasion Protection



Medium Duty

## Durable EN ISO C/ANSI A4 cut-resistant gloves, offering extended glove life

- **Advanced defenses:** Enriched with Lycra® content, the HyFlex® 11-735's liner also benefits from patented INTERCEPT™ Cut Resistance Technology, for EN ISO C/ANSI A4 cut protection
- **Superior durability:** Their palm-dipped PU coating makes for robust PPE gloves with long-lasting resilience, achieving EN level 4 and ANSI level 6 abrasion resistance
- **Lightened comfort:** These HyFlex® gloves' 10G lightweight plaited liner ensures a versatile blend of comfort, flexibility and protection
- **Enhanced grip:** The same polyurethane coating enhances these HyFlex gloves' grip and performance in dry or slightly oily conditions
- **Simplified packaging:** These PU-coated gloves also come in vend pack form, for convenient access in times of need



### Industries

- Automotive
- Machinery and Equipment
- Metal fabrication
- Chemical
- Automotive Aftermarket

### Applications

- Metalworking & assembly operations
- Assembly & inspection of components
- Assembly and disassembly of equipment
- Seizing structural parts
- Mounting and dismantling
- Fastening components, parts
- Loading and unloading trucks and vehicles
- Handling incoming goods
- Maintenance
- Lock smith
- Compatible with consumer and industrial touchscreens

# HyFlex®

ADVANCED MECHANICAL PROTECTION

## 11-735

Tough and durable cut protection with a breathable, soft liner

### Key Features

- **INTERCEPT™ Cut Resistance Technology:** Advanced personal protection
- **Palm-dipped PU coating:** Excellent grip and abrasion resistance
- **10G lightweight plaited liner:** Soft, flexible, Lycra®-imbued comfort

### Vulcanization Chemical Accelerators

- Natural rubber proteins (in knitwrist elastic)

Only a very small number of users may be sensitive to this ingredient(s) and hence may develop irritant and/or allergic contact reactions.

### Performance Standards & Regulatory Compliance



### Technologies

 **INTERCEPT™**  
Cut Resistance Technology



### Specifications

BRAND   STYLE	DESCRIPTION	Gauge	SIZE	LENGTH	COATING COLOR	PACKAGE
HyFlex® 11-735	<b>Finishing:</b> Palm Coated <b>Coating Material:</b> Polyurethane <b>Liner Material:</b> Fiber glass, HPPE, Nylon, Spandex <b>Cuff Style:</b> Knitwrist	10	6, 7, 8, 9, 10, 11	224-269 mm; 8.81-10.59 in	Black	• 12 pairs in a bag; 12 bags in a carton

For additional information visit us at [www.ansell.com](http://www.ansell.com), or call us at

#### Europe, Middle East & Africa Region

Ansell Healthcare Europe NV  
Riverside Business Park  
Blvd International, 55  
1070 Brussels, Belgium  
T: +32 (0) 2 528 74 00  
F: +32 (0) 2 528 74 01

#### Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.  
Blvd. Bernardo Quintana No. 7001-C,  
Q7001 Torre II,  
Suites 1304, 1305 y 1306,  
Col. Centro Sur, c.p. 76079  
Queretaro, Qro. Mexico  
T: +52 442 248 1544 / 248 3133

#### North America Region

Ansell Healthcare Products LLC  
111 Wood Avenue South,  
Suite 900  
Iselin, NJ 08830, USA  
T: +1 800 800 0444  
F: +1 800 800 0445

#### Canada

Ansell Canada  
105 Lauder  
Cowansville, QC J2K 2K8  
Canada  
T: +1 800 363 8340  
F: +1 800 267 3551

#### Australia

Ansell Limited  
Level 3, 678 Victoria Street,  
Richmond, Vic, 3121  
Australia  
T: +61 1800 337 041  
F: +61 1800 803 578

#### Asia Pacific Region

Ansell Global Trading Center  
(Malaysia) Sdn Bhd  
Prima 6, Prima Avenue  
Block 3512, Jalan Teknokrat 6  
T: +603 8310 6688  
F: +603 8310 6699

Ansell, ® and ™ are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending: [www.ansell.com/patentmarking](http://www.ansell.com/patentmarking) © 2024 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.

**Ansell**