



Cut



Light Duty

Durable lightweight industrial gloves, combining advanced cut resistance with superb comfort

- **Advanced protection:** HyFlex® 11-757 light-duty industrial gloves feature INTERCEPT™ Cut Resistance Technology, providing wearers with superior cut resistance at ANSI/ISEA 105-2024 CUT A7 and EN ISO F* levels
- **Enhanced usability:** Their ultra-light, ultra-thin design ensures ample dexterity, breathable comfort and touchscreen compatibility, for uninterrupted daily use and optimized productivity
- **Improved durability:** These HyFlex® gloves' palm-dipped polyurethane coating also delivers excellent abrasion resistance
- **Considered ergonomics:** With a tailored fit at the base of the pinky finger, these safety gloves are shaped around natural hand contours
- **Assured skin-friendliness:** They have also been dermatologically approved by Dermatest®
- **Increased protection:** HyFlex 11-757's palm-dipped coating improves durability, while a reinforced thumb crotch defends against rapid wear
*7x greater than standard ANSI/ISEA 105-2024 CUT A2 and EN ISO B gloves



Industries

- Aerospace
- Automotive
- Machinery and Equipment
- Electronics
- Glass manufacturing
- White Goods

Applications

- Assembly & inspection of components
- Picking, fastening components
- Final assembly
- Applying finish to materials, products
- Applications requiring dexterity and precision
- Handling metal sheets & panels
- Handling of glass sheets, sharpened objects

HyFlex®

ADVANCED MECHANICAL PROTECTION

HyFlex® 11-757

Our lightest ANSI/ISEA 105-2024 CUT A7 and EN ISO F cut resistant glove for touchscreen compatibility

Key Features

- INTERCEPT™ Cut Resistance Technology:** Superior cut resistance*
- Ultra-thin lightweight design:** Dexterity and touchscreen compatibility
- Polyurethane (PU) coating:** Excellent abrasion resistance
- Thumb crotch reinforcement:** Ideal for dry and slightly oily applications
*7x greater than standard ANSI/ISEA 105-2024 CUT A2 and EN ISO B gloves

Performance Standards & Regulatory Compliance

ANSI/ISEA 105-2024



EN388: 2016



3X31F

Technologies



INTERCEPT™
Cut Resistance Technology



Touchscreen Compatible

Specifications

BRAND STYLE	DESCRIPTION	Gauge	SIZE	LENGTH	COATING COLOR	PACKAGE
HyFlex® 11-757	Finishing: Palm dipped, Thumbcrotch reinforcement Coating Material: Polyurethane Liner Material: Nylon, Stainless steel, Polyester, Tungsten Cuff Style: Knitwrist	18	6, 7, 8, 9, 10, 11	222-274 mm / 8.74 - 10.8 inch	Black	12 pairs/bag, 12 bags/carton

For additional information visit us at www.ansell.com, or call us at

Europe, Middle East & Africa Region

Ansell Healthcare Europe NV
Riverside Business Park
Blvd International, 55
1070 Brussels, Belgium
T: +32 (0) 2 528 74 00
F: +32 (0) 2 528 74 01

North America Region

Ansell Healthcare Products LLC
111 Wood Avenue South,
Suite 900
Iselin, NJ 08830, USA
T: +1 800 800 0444
F: +1 800 800 0445

Australia

Ansell Limited
Level 3, 678 Victoria Street,
Richmond, Vic, 3121
Australia
T: +61 1800 337 041
F: +61 1800 803 578

Asia Pacific Region

Ansell Global Trading Center
(Malaysia) Sdn Bhd
Prima 6, Prima Avenue
Block 3512, Jalan Teknokrat 6
T: +603 8310 6688
F: +603 8310 6699

Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.
Blvd. Bernardo Quintana No. 7001-C,
Q7001 Torre II,
Suites 1304, 1305 y 1306,
Col. Centro Sur, c.p. 76079
Queretaro, Qro. Mexico
T: +52 442 248 1544 / 248 3133

Canada

Ansell Canada
105 Lauder
Cowansville, QC J2K 2K8
Canada
T: +1 800 363 8340
F: +1 800 267 3551

Ansell, ® and ™ are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending: www.ansell.com/patentmarking © 2025 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.

Ansell