

Chemical-resistant disposable gloves that offer tough chemical resistance and superior comfort

- **Three-layer design:** Three layers ensure superior protection against harsh chemicals
- **Thin mil design:** Designed to be thinner than standard reusable chemical-resistant gloves (7.8 mil) for protection that allows for better tactility when handling small objects and tools
- **Elevated comfort:** Soft material and ergonomic design offer outstanding fit, feel and flexibility
- **Assured quality:** Their low AQL (0.65) means minimal pinhole defect risks
- **High standards:** Meets EN 374 Type A certified in Europe and KOSHA certified in Korea
- **Retail pack 93-260RP:** Available in convenient packaging of 6 gloves, size specific



Industries

- Aerospace
- Automotive
- Automotive Aftermarket
- Life Sciences
- Chemical
- Agriculture
- Machinery and Equipment
- Metal fabrication
- Utilities
- Warehousing

Recommended For

- Inspection, selecting, checking parts
- Assembly and inspection of components
- Equipment repair and maintenance
- Production line support and maintenance
- General Purpose Auto Aftermarket
- Oil, fluids and filter change
- Blending, compounding solids and liquids
- Sample taking and processing
- Transferring liquids and solids between vessels and tanks and process equipment

TECHNICAL DATA SHEET

	Product Information
Material	Nitrile, Neoprene (Polychloroprene)
External Glove Surface	Textured Fingers
Audit Standards	ISO 9001
Product Certification	Personal Protective Equipment Regulation (EU) 2016/425 Category III risks, EN 388:2016 2000X, CE 0493, EN 421:2010, EN ISO 21420:2020, EN ISO 374-1:2016 Type A JKLOPST, EN ISO 374-5:2016 Virus, FDA21 CFR 177-2600-US Food Contact Approved, ISO 18889:2019, ISO 9001, DOSH-SIRIM certified, Kosha certified, UKCA
Packaging Overview	50 gloves per dispenser 10 dispensers per case 500 gloves per case Retail Pack: 6 gloves per pack; 50 packs per case; 300 gloves per case
Storage Instructions	Keep out of direct sunlight; store in a cool and dry place. Keep away from sources of ozone or ignition.
Country Of Origin	Sri Lanka
Product Segmentation	High Risk
Antistatic	Yes EN1149
Fentanyl Tested	Yes
Silicone Free	Yes
Vulcanization Chemical Accelerators	Zinc Dibutyldithiocarbamate (ZDBC) <i>Only a very small number of users may be sensitive to this ingredient(s) and hence may develop irritant and/or allergic contact reactions.</i>

PHYSICAL PROPERTIES

	Typical Values	Testing Method
Length (mm/inches)	≥ 285 / 11.2	ASTM D3767,EN 420
Freedom from Holes (Inspection level I)	0.65 AQL	ASTM D5151,EN 455-1
Palm Thickness (mm/mils)	0.198/ 7.9	ASTM D3767,EN 420
Finger Thickness (mm/mils)	0.20/ 7.9	ASTM D3767,EN 420
	BEFORE AGINGAFTER AGING	
Ultimate Tensile Strength (MPa)	≥ 14	ASTM D412 & D573
Elongation at Break (%)	≥ 500	ASTM D412
Force at break (N)	≥ 6	EN 455-2

ORDERING INFORMATION

Size	XS (5.5 - 6)	S (6.5 - 7)	M (7.5 - 8)	L (8.5 - 9)	XL (9.5 - 10)	XXL (10.5 - 11)	M (7.5 - 8)	L (8.5 - 9)	XL (9.5 - 10)	XXL (10.5 - 11)
Product Code	93260060	93260070	93260080	93260090	93260100	93260110	93260RP080	93260RP090	93260RP100	93260RP110
Retail Pack Catalog No.			93260RP080	93260RP090	93260RP100		93260RP080	93260RP090	93260RP100	

For additional information visit us at www.ansell.com, or call us at

Europe, Middle East & Africa Region
Ansell Healthcare Europe NV
T: +32 (0) 2 528 74 00
F: +32 (0) 2 528 74 01
info@ansell.com
infochina@ansell.com
JP: +813 5549 8151
info.medical.jp@ansell.com

EN 388
2000X

EN 421
Type A
JKLOPST

EN ISO 374-1:2016
Type A
ISO 18889

North America Region
Ansell Healthcare Products LLC
T: +1 800 800 0444
F: +1 800 300 0444
info@ansell.com
latam.medical@ansell.com
CO: +57 1 288 3247
latam.medical@ansell.com

Latin America, Caribbean & Mexico
BR: +55 (11) 3356 4400
MX: +52 442 296 2050
latam.medical@ansell.com
CO: +57 1 288 3247
latam.medical@ansell.com

ISO 9001

UKCA

Australia
Ansell Limited
T: +61 1800 337 041
F: +61 1800 803 578

Russia
Ansell PYC
Ten. +7 495 258 13 16

