

Previously known as: MICROCHEM® 5000 AVANT AIRline Hood - Model 521

### Ultra-lightweight, air-fed respirator hood ensuring chemical protection.

- **Advanced defenses:** The AlphaTec® 5000 AVANT AIRline HOOD Ultrasonically Welded & Taped - Model 521 provides superb chemical permeation resistance against a wide range of inorganic chemicals
- **Elevated comfort:** This ultra-lightweight hood is fitted with an attached adjustable air flow regulator providing 150 - 300 liters per minute at a working pressure of 3.5 - 5.5 bar
- **Enhanced view:** To improve personal protection, the AlphaTec® 5000 AVANT AIRline HOOD Ultrasonically Welded & Taped - Model 521 features a panoramic visor design with 180-degree view
- **Increased visibility:** Owing to its highly visible orange color, this safety hood also increases workplace safety
- **Added safety:** In addition, it provides an in-built AlphaTec™ Flow Control Valve and Low Flow Alarm unit, which features the AlphaTec™ Low Flow Alarm whistle that produces > 90dB (A) sound pressure and conforms to EN14594: 2005 clause 6.11.



## Industries

- Chemical
- Life Sciences
- Mining
- Energy
- Fire and Rescue


## Applications

- Contaminated Environments
- Chemical Handling
- Filling, blending and charging of raw materials
- Opening and draining pumps valves or lines
- Loading and unloading of process equipment
- Raw material sample collection
- Concentration mixing and palletisation
- Assembly and disassembly of large pipes
- Unexpected leakages spills or other releases


## KEY FEATURES & BENEFITS

- **Superb chemical resistance:** Protects from various inorganic chemicals
- **Ultra-lightweight:** Increased comfort for extended wear
- **Panoramic visor design:** For unhindered 180-degree view

## Material Diagram



## Seam Diagram



Performance Standards

  
0598

  
PARTIAL BODY  
PROTECTION ONLY

  
TYPE PB [3]

  
TYPE PB [4]

  
EN 14126

EN 14594:2005 Class 4A

Product Information

Product Information	
Available Sizes	One Size
Color	Orange
Country Of Origin	China
Packaging Overview	Individually Packed
Product Material	Multi-layer non-woven barrier Laminate fabric
Product Reference	5000 AVANT AIRline Hood - Model 521
Standards Overview	CE CATEGORY III (Type PB [3]-B, Type PB [4]-B, EN 1073-1, EN 14126, EN 14594)
Seam Type	Welded and Taped
Shelf Life	5 years
Style Number	O500521

Suit components & accessories

Suit Components and Accessories	
Design Features	AlphaTec® 5000 AVANT Air-Fed Hood c/w belt mounted AlphaTec® flow control valve and low flow warning whistle. Flow rate adjustable from 150 to 300 litres per minute at a working pressure of 3 to 5 bar. T000(O521) version has a 1/4" female parallel thread for addition of the users preferred airline connector. TA00(A521) version comes with pre-fitted CEJN-342 Connector. TB00(B521) version comes with a pre-fitted AQR06 Connector. Panoramic PET Semi rigid multi-layer visor. Polyester waist belt and YKK buckle.

For additional in formation visit us at [www.ansell.com](http://www.ansell.com), or call us at

**Europe, Middle East & Africa Region**  
Ansell Healthcare Europe NV  
T: +32 (0) 2 528 74 00

**North America Region**  
Ansell Healthcare Products LLC  
T: +1 800 800 0444

**Australia**  
Ansell Limited  
T: +61 1800 337 041

**Asia Pacific Region**  
Ansell Global Trading Center  
T: +603 8310 6688

**Latin America & Caribbean Region**  
Ansell Commercial Mexico S.A. de C.V.  
T: +52 442 248 1544 / 248 3133

Ansell, ® and ™ are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending: [www.ansell.com/patentmarking](http://www.ansell.com/patentmarking) © 2025 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.

