

Black nitrile exam gloves for dirt-masking hand protection and superior grip

- **Masks stains:** MICROFLEX® 93-852 exam gloves' black color disguises dirt while enhancing the visibility of light-colored objects
- **Enhanced grip:** A fully textured, non-foaming design ensures these powder- and silicone-free nitrile gloves have superior grip
- **Proven protection:** These medical exam gloves are approved for use against fentanyl and gastric acid (vomit), ensuring they are suitable for hazardous overdose situations — they also comply with EN ISO 374 Type B chemical resistance standards for chemical splash protection
- **Genuine versatility:** These gloves are suitable for various applications, used notably by auto mechanics, maintenance workers and law enforcement officers
- **Food handling compliant:** Also ideal for a wide range of food handling applications



Industries

- Automotive
- Automotive Aftermarket
- Life Sciences
- Machinery and Equipment

Recommended For

- Inspection, selecting, checking parts
- General Purpose Auto Aftermarket
- Use of cleaning tools and robotic equipment
- Oil, fluids and filter change
- Engine transmission and repair
- Tire rotation & changes
- Maintaining lab furniture and equipment
- Sample taking and processing
- Blending, compounding solids and liquids
- Raw material sample collection
- Weighing and dispensing of solid and liquid raw materials
- Inspection (picking, checking and marking)

TECHNICAL DATA SHEET

	Product Information
Material	Nitrile
External Glove Surface	Fully Textured
Audit Standards	ISO 13485:2003
Product Certification	Medical Device Regulation (EU) 2017/745 Class I, Personal Protective Equipment Regulation (EU) 2016/425 Category III risks, CE 0493, EC 2023/2006, EC 1935/2004, EN 455 1-4, EN ISO 21420:2020, EN ISO 374-1:2016 Type B JKT, EN ISO 374-5:2016 Virus, ISO 11193, ISO 18889:2019, UKCA, EU Food Contact Approved
Packaging Overview	100 gloves per dispenser 10 dispensers per case 1000 gloves per case
Storage Instructions	Keep out of direct sunlight; store in a cool and dry place. Keep away from sources of ozone or ignition.
Country Of Origin	Malaysia
Product Segmentation	Robust
Antistatic	Yes EN1149
Silicone Free	Yes


PHYSICAL PROPERTIES

	Typical Values		Testing Method
Length (mm/inches)	245 / 9.6		ASTM D3767,EN 420
Freedom from Holes (Inspection level I)	1.5 AQL		ASTM D5151,EN 455-2
Palm Thickness (mm/mils)	0.11 / 4.3		ASTM D3767,EN 420
Finger Thickness (mm/mils)	0.15 / 5.9		ASTM D3767,EN 420
	BEFORE AGING	AFTER AGING	
Ultimate Tensile Strength (MPa)	24	20	ASTM D412 & D573
Elongation at Break (%)	600	500	ASTM D412
Force at break (N)	7	6	EN 455-2

ORDERING INFORMATION

Size	XS (5.5 - 6)	S (6.5 - 7)	M (7.5 - 8)	L (8.5 - 9)	XL (9.5 - 10)	XXL (10.5 - 11)
Product Code	93852060	93852070	93852080	93852090	93852100	93852110

Performance Standards and Regulatory Compliance



For additional information visit us at www.ansell.com, or call us at

Europe, Middle East & Africa Region Ansell Healthcare Europe NV T: +32 (0) 2 528 74 00 F: +32 (0) 2 528 74 01 Asia Pacific Region MY: +603 8310 6688 apac.medical@ansell.com CN: +86 21 38275000 infochina@ansell.com JP: +813 5549 8151 info.medical.jp@ansell.com	North America Region Ansell Healthcare Products LLC T: +1 800 800 0444 F: +1 800 800 0445 Latin America & Caribbean Region BR: +55 (11) 3356-3100 latam.medical@ansell.com MX: +52 442 296 2050 latam.medical@ansell.com CO: +57 1 288 3247 latam.medical@ansell.com	Australia Ansell Limited T: +61 1800 337 041 F: +61 1800 803 578 Russia Ansell PYC Ten. +7 495 258 13 16
---	--	--

Ansell, ® and ™ are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending: www.ansell.com/patentmarking © 2025 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.

