

## An unparalleled combination of chemical splash protection, comfort and durability

- **World leader:** TouchNTuff® 92-600 gloves are the world's leading disposable gloves for chemical splash protection
- **Superior protection:** Made with TNT™ Chemical Splash Resistance Technology, these gloves effectively safeguard hands from exposure to harmful chemicals
- **Elevated comfort:** Super soft nitrile provides a comfortable feel during extended wear
- **Robust durability:** Proprietary formulation is extra-strong to prevent tearing during heavy-duty work
- **Prevents surface defects:** Silicone-free, they prevent contaminant transfer that causes flaws in paints, coatings and finishes



### Industries

- Life Sciences
- Food Processing
- Automotive
- Machinery and Equipment
- Chemical
- Agriculture
- Utilities
- Warehousing

### Recommended For

- Transferring liquids and solids
- Sample taking and processing
- Meat, Fish and Food Processing
- Industrial Production
- Maintenance
- Laboratory analysis
- Chemical Handling

TECHNICAL DATA SHEET

|                        | Product Information                                                                                      |
|------------------------|----------------------------------------------------------------------------------------------------------|
| External Glove Surface | Smooth                                                                                                   |
| Audit Standards        | ISO 9001                                                                                                 |
| Packaging Overview     | 100 gloves per dispenser<br>10 dispensers per case<br>1000 gloves per case                               |
| Storage Instructions   | Keep out of direct sunlight; store in a cool and dry place. Keep away from sources of ozone or ignition. |
| Country Of Origin      | Sri Lanka, Thailand                                                                                      |
| Product Segmentation   | Robust                                                                                                   |
| Antistatic             | Yes EN1149                                                                                               |

PHYSICAL PROPERTIES

|                                            | Typical Values                                                                         |             | Testing Method      |
|--------------------------------------------|----------------------------------------------------------------------------------------|-------------|---------------------|
| Length (mm/inches)                         | 240 / 9.5                                                                              |             | ASTM D3767,EN 420   |
| Freedom from Holes<br>(Inspection level I) | 4.0 AQL (North & South America) / 1.5 AQL (Europe, Middle East, Africa, Asia, Pacific) |             | ASTM D5151,EN 455-1 |
| Palm Thickness (mm/mils)                   | 0.125 / 4.9                                                                            |             | ASTM D3767,EN 420   |
| Finger Thickness (mm/mils)                 | 0.14 / 5.5                                                                             |             | ASTM D3767,EN 420   |
|                                            | BEFORE AGING                                                                           | AFTER AGING |                     |
| Ultimate Tensile Strength (MPa)            | ≥ 18                                                                                   | ≥ 18        | ASTM D412 & D573    |
| Elongation at Break (%)                    | ≥ 500                                                                                  | ≥ 400       | ASTM D412           |
| Force at break (N)                         | ≥ 6                                                                                    | ≥ 6         | EN 455-2            |

ORDERING INFORMATION

| Size         | S (6.5 - 7) | M (7.5 - 8) | L (8.5 - 9) | XL (9.5 - 10) |
|--------------|-------------|-------------|-------------|---------------|
| Product Code | 92600070    | 92600080    | 92600090    | 92600100      |

Performance Standards and Regulatory Compliance



For additional information visit us at [www.ansell.com](http://www.ansell.com), or call us at

**Europe, Middle East & Africa Region**  
Ansell Healthcare Europe NV  
T: +32 (0) 2 528 74 00  
F: +32 (0) 2 528 74 01  
  
**Asia Pacific Region**  
MY: +603 8310 6688  
apac.medical@ansell.com  
CN: +86 21 38275000  
infochina@ansell.com  
JP: +813 5549 8151  
info.medical.jp@ansell.com

**North America Region**  
Ansell Healthcare Products LLC  
T: +1 800 800 0444  
F: +1 800 800 0445  
  
**Latin America & Caribbean Region**  
BR: +55 (11) 3356-3100  
latam.medical@ansell.com  
MX: +52 442 296 2050  
latam.medical@ansell.com  
CO: +57 1 288 3247  
latam.medical@ansell.com

**Australia**  
Ansell Limited  
T: +61 1800 337 041  
F: +61 1800 803 578  
  
**Russia**  
Ansell PYC  
Ten. +7 495 258 13 16

Technology



Ansell, ® and ™ are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending: [www.ansell.com/patentmarking](http://www.ansell.com/patentmarking) © 2024 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.

