

## Extra-thick disposable latex gloves, offering durable protection for heavy-duty applications

- **Extra defense:** MICROFLEX® 63-293 latex gloves are 3x thicker than standard disposable latex gloves, ensuring greater resistance against snags and tears
- **Comfortable fit:** These thick latex gloves' soft, elastic formulation delivers comfort and flexibility
- **Added protection:** With an extended cuff, these gloves offer workers enhanced forearm and wrist protection
- **Enhanced grip:** MICROFLEX® 63-293 gloves' textured fingertips enhance grip performance
- **Easy donning:** Donning is made easy thanks to the gloves' double-chlorinated design



**\*CAUTION:** This product contains natural rubber latex, which may cause allergic reactions

### Industries

- Automotive
- Automotive Aftermarket
- Life Sciences
- Healthcare

### Recommended For

- Inspection, selecting, checking parts
- Assembly and inspection of components
- Picking and fastening components
- Equipment repair and maintenance
- General Purpose Auto Aftermarket
- Body panel repair and replacement
- Tire rotation & changes
- Animal care feeding and cleanup
- Maintaining lab furniture and equipment
- Sample taking and processing
- Raw material sample collection
- Extra protection over the wrist and arm

TECHNICAL DATA SHEET

	Product Information
Material	Natural Rubber Latex
External Glove Surface	Textured Fingers
Audit Standards	EN ISO 13485:2012
Product Certification	EN ISO 374-1:2016 Type B KPT, EN 374:2003 Low Chemical Resistant, EN ISO 374-5:2016 Virus, EN 374:2003 Microorganism, Category III, EN 420:2003 + A1:2009, European Directive 89/686/EEC, EC 2023/2006, EU Food Contact Approved, EN 421:2010 Radioactive Contamination, EN ISO 21420:2020
Packaging Overview	50 gloves per dispenser 10 dispensers per case 500 gloves per case
Storage Instructions	Keep out of direct sunlight; store in a cool and dry place. Keep away from sources of ozone or ignition.
Country Of Origin	Malaysia
Product Segmentation	High Risk
Antistatic	Not Tested
Silicone Free	No

PHYSICAL PROPERTIES

	Typical Values		Testing Method
Length (mm/inches)	295 / 11.6		ASTM D3767,EN 420
Freedom from Holes (Inspection level I)	1.5 AQL		ASTM D5151,EN 455-1
Palm Thickness (mm/mils)	0.28/11		ASTM D3767,EN 420
Finger Thickness (mm/mils)	0.36/14.2		ASTM D3767,EN 420
	BEFORE AGING	AFTER AGING	
Ultimate Tensile Strength (MPa)	≥ 34	≥ 21	ASTM D412 & D573
Elongation at Break (%)	≥ 850	≥ 750	ASTM D412
Force at break (N)	≥ 15	≥ 10	EN 455-2

ORDERING INFORMATION

Size	S (6.5 - 7)	M (7.5 - 8)	L (8.5 - 9)	XL (9.5 - 10)
Product Code	63293070	63293080	63293090	63293100

Performance Standards and Regulatory Compliance



For additional information visit us at [www.ansell.com](http://www.ansell.com), or call us at

Europe, Middle East & Africa Region  
Ansell Healthcare Europe NV  
T: +32 (0) 2 528 74 00  
F: +32 (0) 2 528 74 01

Asia Pacific Region  
MY +603 8310 6688  
apac.medical@ansell.com  
CN: +86 21 38275000  
infochina@ansell.com  
JP: +813 5549 8151  
info.medical.jp@ansell.com

North America Region  
Ansell Healthcare Products LLC  
T: +1 800 800 0444  
F: +1 800 800 0445

Latin America & Caribbean Region  
BR +55 (11) 3356-3100  
latam.medical@ansell.com  
MX: +52 442 296 2050  
latam.medical@ansell.com  
CO: +57 1 288 3247  
latam.medical@ansell.com

Australia  
Ansell Limited  
T: +61 1800 337 041  
F: +61 1800 803 578

Russia  
Ansell PYC  
Ten. +7 495 258 13 16

Ansell, ® and ™ are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending: [www.ansell.com/patentmarking](http://www.ansell.com/patentmarking) © 2025 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.

