

## Durable protection in a comfortable, versatile glove

- **Genuine versatility:** Designed for versatility, these nitrile gloves are ideal for a wide variety of industries in mid-duty applications
- **Secure grip:** Textured throughout the palm to ensure good grip in wet, dry and oily environments
- **Specialized protection:** The MICROFLEX™ 93-143 gloves have been tested for use with chemotherapy drugs\*
- **Silicone-free:** These gloves are also silicone-free, allowing for better product protection



\*see product packaging for details

### Industries

- Automotive
- Life Sciences
- Food Processing

### Recommended For

- Transferring liquids and solids
- Sample taking and processing
- Light assembly tasks
- Handling of paint/glue guns and sprayers
- Handling of tools
- Laboratory analysis
- Food processing and handling
- Assembly and inspection of components
- Chemical Handling
- Cleaning of plant and machines
- Blending, compounding materials
- Equipment repair and maintenance
- Maintenance

## TECHNICAL DATA SHEET

|                        | Product Information                                                                                                                                                                                                                                                                                                                                    |
|------------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Material               | Nitrile                                                                                                                                                                                                                                                                                                                                                |
| External Glove Surface | Fully Textured                                                                                                                                                                                                                                                                                                                                         |
| Audit Standards        | ISO 13485, ISO 9001                                                                                                                                                                                                                                                                                                                                    |
| Product Certification  | Medical Device Regulation (EU) 2017/745 Class I, Personal Protective Equipment Regulation (EU) 2016/425 Category III risks, ASTM D6319, EU Food Contact Approved, EC 2002/72, EC 2023/2006, EN ISO 21420:2020, EN ISO 374-1:2016 Type B KPT, EN ISO 374-5:2016 Virus, FDA21 CFR 177-2600-US Food Contact Approved, ISO 13485, ISO 18889:2019, ISO 9001 |
| Packaging Overview     | 100 gloves per dispenser<br>10 dispensers per case<br>1000 gloves per case                                                                                                                                                                                                                                                                             |
| Storage Instructions   | Keep out of direct sunlight; store in a cool and dry place. Keep away from sources of ozone or ignition.                                                                                                                                                                                                                                               |
| Country Of Origin      | Malaysia                                                                                                                                                                                                                                                                                                                                               |
| Product Segmentation   | Multi-Purpose                                                                                                                                                                                                                                                                                                                                          |
| Antistatic             | Yes                                                                                                                                                                                                                                                                                                                                                    |
| Silicone Free          | Yes                                                                                                                                                                                                                                                                                                                                                    |

## PHYSICAL PROPERTIES

|                                         | Typical Values |             | Testing Method      |
|-----------------------------------------|----------------|-------------|---------------------|
| Length (mm/inches)                      | 240 / 9.45     |             | ASTM D3767,EN 420   |
| Freedom from Holes (Inspection level I) | 1.5 AQL        |             | ASTM D5151,EN 374-2 |
| Palm Thickness (mm/mils)                | 0.11 / 4.3     |             | ASTM D3767,EN 420   |
| Finger Thickness (mm/mils)              | 0.12 / 4.7     |             | ASTM D3767,EN 420   |
|                                         | BEFORE AGING   | AFTER AGING |                     |
| Elongation at Break (%)                 | 500            | 400         | ASTM D412           |
| Force at break (N)                      | 6              | 6           | EN 455-2            |

ORDERING INFORMATION

| Size         | XS (5.5 - 6) | S (6.5 - 7) | M (7.5 - 8) | L (8.5 - 9) | XL (9.5 - 10) |
|--------------|--------------|-------------|-------------|-------------|---------------|
| Product Code | 93143060     | 93143070    | 93143080    | 93143090    | 931430100     |

Performance Standards and Regulatory Compliance



K P T

VIRUS

ISO 13485

ISO 18889

ISO 9001

For additional information visit us at [www.ansell.com](http://www.ansell.com), or call us at

**Europe, Middle East & Africa Region**

Ansell Healthcare Europe NV

T: +32 (0) 2 528 74 00

F: +32 (0) 2 528 74 01

**Asia Pacific Region**

MY: +603 8310 6688

apac.medical@ansell.com

CN: +86 21 38275000

infochina@ansell.com

JP: +813 5549 8151

info.medical.jp@ansell.com

**North America Region**

Ansell Healthcare Products LLC

T: +1 800 800 0444

F: +1 800 800 0445

**Latin America & Caribbean Region**

BR: +55 (11) 3356-3100

latam.medical@ansell.com

MX: +52 442 296 2050

latam.medical@ansell.com

CO: +57 1 288 3247

latam.medical@ansell.com

**Australia**

Ansell Limited

T: +61 1800 337 041

F: +61 1800 803 578

**Russia**

Ansell PYC

Ten. +7 495 258 13 16

Ansell, ® and ™ are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending: [www.ansell.com/patentmarking](http://www.ansell.com/patentmarking) © 2025 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.

