

Ergonomically designed to reduce hand fatigue

- **ERGOFORM[™] Technology:** MICROFLEX[®] XCEED[®] 93-733 gloves are designed with proprietary ergonomic design technology to support musculoskeletal health and increase worker productivity
- **Exceptional tactile sensitivity:** These lightweight, yet strong, nitrile gloves offer a thin design for enhanced tactile sensitivity
- **Strong barrier integrity:** With a low 0.65 AQL, these gloves offer advanced barrier integrity
- **Strong formulation:** MICROFLEX[®] XCEED[®] 93-733 gloves are designed to prevent rips and tears
- **Reduced waste:** Gloves are smartly packaged, with 250 gloves* per box and easy, single glove dispensing to reduce waste



*230 gloves per box for size XL

Industries

- Automotive Aftermarket
- Food Processing
- Life Sciences

Recommended For

- General Purpose Auto Aftermarket
- Plant disinfection and sanitization
- All food processing, applications that have food contact
- Assembly of parts
- Sample taking and processing
- Raw material sample collection
- Enhanced tactile sensitivity and dexterity, especially for delicate procedures
- Protection from Type IV chemical allergies in HCW's or patients

TECHNICAL DATA SHEET

	Product Information
External Glove Surface	Textured Fingers
Audit Standards	ISO 13485, ISO 9001
Product Certification	Medical Device Regulation (EU) 2017/745 Class I, Personal Protective Equipment Regulation (EU) 2016/425 Category III risks
Packaging Overview	250 gloves per dispenser 10 dispensers per case 2500 gloves per case
Storage Instructions	Keep out of direct sunlight; store in a cool and dry place. Keep away from sources of ozone or ignition.
Country Of Origin	Malaysia
Product Segmentation	High Touch
Antistatic	Yes

PHYSICAL PROPERTIES

	Typical Values		Testing Method
Length (mm/inches)	240 / 9.5		ASTM D3767,EN 420
Freedom from Holes (Inspection level I)	0.65 AQL		ASTM D5151,EN 374-2
Palm Thickness (mm/mils)	0.07 / 2.8		ASTM D3767,EN 420
Finger Thickness (mm/mils)	0.11 / 4.3		ASTM D3767,EN 420
	BEFORE AGING	AFTER AGING	
Ultimate Tensile Strength (MPa)	22	14	
Elongation at Break (%)	≥ 500	≥ 400	
Force at break (N)	≥ 6	≥ 6	

ORDERING INFORMATION

Size	XS (5.5 - 6)	S (6.5 - 7)	M (7.5 - 8)	L (8.5 - 9)	XL (9.5 - 10)
Product Code	93733060	93733070	93733080	93733090	93733100

Performance Standards and Regulatory Compliance

EN ISO 374-1:2016
Type B


K P T

EN ISO 374-5


VIRUS

ISO 13485



ISO 9001



For additional information visit us at www.ansell.com, or call us at

Europe, Middle East & Africa Region
Ansell Healthcare Europe NV
T: +32 (0) 2 528 74 00
F: +32 (0) 2 528 74 01

Asia Pacific Region
MY: +603 8310 6688
apac.medical@ansell.com
CN: +86 21 38275000
infochina@ansell.com
JP: +813 5549 8151
info.medical.jp@ansell.com

North America Region
Ansell Healthcare Products LLC
T: +1 800 800 0444
F: +1 800 800 0445

Latin America & Caribbean Region
BR: +55 (11) 3356-3100
latam.medical@ansell.com
MX: +52 442 296 2050
latam.medical@ansell.com
CO: +57 1 288 3247
latam.medical@ansell.com

Australia
Ansell Limited
T: +61 1800 337 041
F: +61 1800 803 578

Russia
Ansell PYC
Ten. +7 495 258 13 16

Technology

Ansell, ® and ™ are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending: www.ansell.com/patentmarking © 2024 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.