



BioClean™ Clearview Autoclavable Goggles BCAP

Clearview autoclave panoramic goggles, for excellent optical clarity

- **Maximized vision:** BioClean™ Clearview Autoclavable Goggles BCAP feature an anti-fog lens that is both deep and extra-wide, for an increased field of vision
- **Reduced contamination risks:** These BioClean™ clearview goggles are processed in a NEBB-certified ISO Class 4 environment and possess an indirect ventilation system to reduce the risk of contamination
- **Improved durability:** These autoclavable goggles' robust design can withstand 40 autoclave cycles for housing of 30 minutes duration at 121°C/250°F. Anti-fog performance remaining for up to 25 autoclave cycles for lens (anti-fogging) with no signs of degradation (under laboratory conditions)
- **Enhanced comfort:** These autoclavable cleanroom goggles are constructed with a super-soft thermoplastic rubber frame, non-linting latex-free silicone headband, and polypropylene hooks suitable to be worn over eyeglasses



Key Features and Benefits

- ◊ **Panoramic, wide-angle lens:** For a deeper, wider field of vision
- ◊ **Indirect ventilation system:** Reduced risks of contamination
- ◊ **Autoclave-resistant design:** For durable clearview goggles

Industries

- Controlled and Critical Environments
- Laboratory and Research
- Production and Manufacturing

Recommended For

- Clean room cleaning and preparing
- Semiconductor manufacturing
- White goods assembly
- Medical Device Manufacturing
- Organic and material synthesis
- Preparing pharmaceutical products
- Nutraceutical manufacturing
- Biotechnologies Blending operations



BioClean™ Clearview Autoclavable Goggles BCAP

TECHNICAL DATA SHEET

PRODUCT INFORMATION

Material	Thermoplastic rubber, Polycarbonate, Silicone, Polypropylene
Color	White
Audit Standards	Manufacturing QMS Audit Standards ISO 9001
Standards	CE Number, EN 166:2001, Category II, UKCA
Packaging Overview	Goggle (BCAP & BCAP-1): One piece per sealed PE bag (to be removed prior to autoclaving); 12 bags per inner box; five boxes per carton (60 pieces). Replacement Lens (BCAP-SL): One piece per sealed PE bag; 10 bags per inner box; 10 boxes per carton (100 pieces) Replacement Strap (BCAP-SS)*: 25 pieces per sealed PE bag; two bags per inner box; 10 boxes per carton (500 pieces) *Each individual strap includes adjuster hooks and strap clips.
Cleanroom Class	Class 10/ISO 4 & EU GMP Grade A
Shelf Life	5 years
Classification	EN166
Optical Class	1
Storage Instructions	Keep away from direct sunlight; store in a dry place and keep in the original packaging. Keep away from ozone sources. If products are properly stored, as indicated, they won't lose their performances or change characteristics significantly. If products could be affected by ageing or storage, the expiry date is mentioned on the packaging materials.

PHYSICAL PROPERTIES

Overall Dimensions	Lens Thickness ($\pm 0.3\text{mm}$): 2.1mm Bridge Width ($\pm 0.5\text{mm}$): 50mm Bridge Height ($\pm 0.5\text{mm}$): 25mm Overall Width (hinge to hinge) ($\pm 3\text{mm}$): 160mm Overall Height ($\pm 3\text{mm}$): 85mm Overall Weight: 103g
--------------------	---

ORDERING INFORMATION

	SIZE	Panoramic Autoclavable Goggles	Replacement Lens	Replacement Strap
BCAP	REORDER NO.	BCAP	BCAP-SL	BCAP-SS



BioClean™ Clearview Autoclavable Goggles BCAP

EXPLANATION OF FRAME MARKINGS

Required Markings	Markings On Frame	Meaning
Manufacturers Identification's Mark	Ansell	Ansell
Brand	BioClean™	BioClean™
Standard Number	EN166	European Standard on Personal Eye Protection
Field of Use	3	Liquids (droplets or splashes)
Field of Use	BT	Medium energy impact at extremes of temperature
Conformity Mark	CE	Conformity with European Standards
Field of Use	UKCA	Conformity with Great Britain Standard

EXPLANATION OF OCULAR MARKINGS

Required Markings	Markings On Ocular	Meaning
Manufacturers Identification's Mark	BioClean™	BioClean™
Optical Class	1	High optical quality
Mechanical Strength	BT	Medium energy impact at extremes of temperature
Field of Use	N	Resistance to fogging
Field of Use	O	Original ocular
Original Or Replacement Ocular	▽	Replacement Ocular

For additional information visit us at www.ansell.com, or call us at

Europe, Middle East & Africa Region

Ansell Healthcare Europe NV
T: +32 (0) 2 528 74 00
F: +32 (0) 2 528 74 01

Asia Pacific Region

Ansell Global Trading Center
T: +603 8310 6688
F: +603 8310 6699

North America Region

Ansell Healthcare Products LLC
US T: +1 800 800 0444
US F: +1 800 800 0445
CA T: +1-800-363-8340

Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.
T: +52 442 248 1544 / 248 3133

Australia

Ansell Limited
T: +61 1800 337 041
F: +61 1800 803 578

UK

Ansell Nitritex
T: +44 1638 663338
F: +44 1638 668890

Performance Standards and
Regulatory Compliance



Ansell, ® and ™ are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending:
www.ansell.com/patentmarking © 2025 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.

