

## Thick natural latex rubber gloves, granting superior protection for heavy-duty applications

- **Advanced defenses:** With 0.73mm/29 mil thickness, AlphaTec® 87-950 black protective gloves are 50% thicker than standard flock-lined gloves, for greater durability and superb mechanical and chemical resistance\*
- **Increased comfort:** Thanks to their pure cotton flock lining, AlphaTec® 87-950 hand protection gloves also absorb perspiration, keeping hands dry and comfortable with sustained wear
- **Enhanced cleanliness:** These chemical-resistant gloves also undergo an external chlorination treatment, for added cleanliness
- **Assured quality:** In addition, they boast an AQL of 1.5

*\*protects against ketones, salts, detergents, alcohols, alkalis and fats*

### Industries

- Construction
- Machinery and Equipment
- Infrastructure Maintenance
- Chemical

### Applications

- Maintenance of plant and heavy equipment
- Chemical processing and preparation
- Janitorial use



Previously known as: Extra 87-950

### Key Features

- **Thick natural rubber latex:** Superb mechanical and chemical protection\*
- **100% cotton flock lining:** For safety gloves offering drier comfort
- **External chlorination treatment:** Harder surface, added cleanliness

\*protects against ketones, salts, detergents, alcohols, alkalis and fats

### Vulcanization Chemical Accelerators

- Natural rubber proteins
- Zinc Diethyldithiocarbamate

Only a very small number of users may be sensitive to this ingredient(s) and hence may develop irritant and/or allergic contact reactions.

### Performance Standards



### Specifications

| BRAND   STYLE    | DESCRIPTION                                   | SIZE              | Length (MM/INCHES) | COLOR | PACKAGE                                                                                |
|------------------|-----------------------------------------------|-------------------|--------------------|-------|----------------------------------------------------------------------------------------|
| AlphaTec® 87-950 | <b>Coating Material:</b> Natural Rubber Latex | 7.5, 8, 9, 10, 11 | 325 / 12.8         | Black | <ul style="list-style-type: none"> <li>12 pairs per bag, 12 bags per carton</li> </ul> |

#### Europe, Middle East & Africa Region

Ansell Healthcare Europe NV  
Riverside Business Park  
Blvd International, 55  
1070 Brussels, Belgium  
T: +32 (0) 2 528 74 00  
F: +32 (0) 2 528 74 01

#### North America Region

Ansell Healthcare Products LLC  
111 Wood Avenue South,  
Suite 210  
Iselin, NJ 08830, USA  
T: +1 800 800 0444  
F: +1 800 800 0445

#### Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.  
Blvd. Bernardo Quintana No. 7001-C,  
Q7001 Torre II,  
Suites 1304, 1305 y 1306,  
Col. Centro Sur, c.p. 76079  
Queretaro, Qro. Mexico  
T: +52 442 248 1544 / 248 3133

#### Canada

Ansell Canada Inc.  
105, rue Lauder  
Cowansville (Québec)  
J2K 2K8, Canada  
T: 1 800 363-8340  
F: 1 888 267-3551

Ansell, ® and "™" are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending:  
[www.ansell.com/patentmarking](http://www.ansell.com/patentmarking) © 2025 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.