

## Ergonomically designed to reduce hand fatigue

- **Reduced allergy risk:** MICROFLEX® 93-833 gloves are manufactured without accelerators for low dermatitis potential. These gloves prevent instances of Type I latex allergies and Type IV chemical allergic reactions
- **Extra durability:** stronger formulation to protect against rips and tears while keeping the same tactile sensitivity
- **Enhanced comfort:** softer formulation for a lightweight, softer skin feel
- **ERGOFORM™ Technology:** designed with proprietary ergonomic design technology to support musculoskeletal health and increase worker productivity
- **Reduced waste:** Gloves are smartly packaged, with 250 gloves per box and easy, single glove dispensing to reduce waste
- **Strong barrier integrity:** With a low 0.65 AQL, these gloves offer advanced barrier integrity



### Industries

- Automotive Aftermarket
- Food Processing
- Life Sciences
- Healthcare
- Machinery and Equipment
- Metal fabrication

### Recommended For

- General Purpose Auto Aftermarket
- All food processing, applications that have food contact
- Assembly of parts
- Sample taking and processing
- Enhanced tactile sensitivity and dexterity, especially for delicate procedures
- Extra comfort during long, sustained procedures
- Protection from Type I latex allergy in HCW's or patients
- Protection from Type IV chemical allergies in HCW's or patients
- Standard patient examinations

TECHNICAL DATA SHEET

|                                     | Product Information                                                                                                                                                                                                                                                                                                                                                                                                                                     |
|-------------------------------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Material                            | Nitrile                                                                                                                                                                                                                                                                                                                                                                                                                                                 |
| External Glove Surface              | Textured Fingers                                                                                                                                                                                                                                                                                                                                                                                                                                        |
| Audit Standards                     | ISO 13485, ISO 9001                                                                                                                                                                                                                                                                                                                                                                                                                                     |
| Product Certification               | Medical Device Regulation (EU) 2017/745 Class I, Personal Protective Equipment Regulation (EU) 2016/425 Category III risks, ASTM D6319, CE 0493, EC 1935/2004, EC 2023/2006, EN 1149-1/2/3, EN 16523-1, EN ISO 374-5:2016 Virus, EN ISO 21420:2020, EN ISO 374-1:2016 Type B KPT, EN 421:2010, EN 455 1-4, FDA21 CFR 177-2600-US Food Contact Approved, EU Food Contact Approved, ISO 13485, ISO 9001, PMDA Notification Number: 13B3X10307AH0001, UKCA |
| Packaging Overview                  | 250 gloves per dispenser<br>10 dispensers per case<br>2500 gloves per case<br>XL: 230 gloves per dispenser                                                                                                                                                                                                                                                                                                                                              |
| Storage Instructions                | Keep out of direct sunlight; store in a cool and dry place. Keep away from sources of ozone or ignition.                                                                                                                                                                                                                                                                                                                                                |
| Country Of Origin                   | Malaysia                                                                                                                                                                                                                                                                                                                                                                                                                                                |
| Product Segmentation                | High Touch                                                                                                                                                                                                                                                                                                                                                                                                                                              |
| Antistatic                          | Yes                                                                                                                                                                                                                                                                                                                                                                                                                                                     |
| Silicone Free                       | No                                                                                                                                                                                                                                                                                                                                                                                                                                                      |
| Vulcanization Chemical Accelerators | <ul style="list-style-type: none"><li>Made without accelerators</li></ul> <p><i>Only a very small number of users may be sensitive to this ingredient(s) and hence may develop irritant and/or allergic contact reactions.</i></p>                                                                                                                                                                                                                      |

PHYSICAL PROPERTIES

|                                         | Typical Values |             | Testing Method      |
|-----------------------------------------|----------------|-------------|---------------------|
| Length (mm/inches)                      | 240 / 9.5      |             | ASTM D3767,EN 420   |
| Freedom from Holes (Inspection level I) | 0.65 AQL       |             | ASTM D5151,EN 455-1 |
| Palm Thickness (mm/mils)                | 0.07 / 2.8     |             | ASTM D3767,EN 420   |
| Finger Thickness (mm/mils)              | 0.11 / 4.3     |             | ASTM D3767,EN 420   |
|                                         | BEFORE AGING   | AFTER AGING |                     |
| Ultimate Tensile Strength (MPa)         | ≥ 26           | ≥ 22        | ASTM D412 & D573    |
| Elongation at Break (%)                 | ≥ 500          | ≥ 400       | ASTM D412           |
| Force at break (N)                      | ≥ 6            | ≥ 6         | EN 455-2            |

ORDERING INFORMATION

| Size         | XS (5.5 - 6) | S (6.5 - 7) | M (7.5 - 8) | L (8.5 - 9) | XL (9.5 - 10) |
|--------------|--------------|-------------|-------------|-------------|---------------|
| Product Code | 93833060     | 93833070    | 93833080    | 93833090    | 93833100      |

Performance Standards and Regulatory Compliance



For additional information visit us at [www.ansell.com](http://www.ansell.com), or call us at

|                                                                                                                                                                                                                                                                                                                        |                                                                                                                                                                                                                                                                                                                         |                                                                                                                                              |
|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|----------------------------------------------------------------------------------------------------------------------------------------------|
| <b>Europe, Middle East &amp; Africa Region</b><br>Ansell Healthcare Europe NV<br>T: +32 (0) 2 528 74 00<br>F: +32 (0) 2 528 74 01<br><br><b>Asia Pacific Region</b><br>MY +603 8310 6688<br>apac.medical@ansell.com<br>CN: +86 21 38275000<br>infochina@ansell.com<br>JP: +813 5549 8151<br>info.medical.jp@ansell.com | <b>North America Region</b><br>Ansell Healthcare Products LLC<br>T: +1 800 800 0444<br>F: +1 800 800 0445<br><br><b>Latin America &amp; Caribbean Region</b><br>BR +55 (11) 3356-3100<br>latam.medical@ansell.com<br>MX: +52 442 296 2050<br>latam.medical@ansell.com<br>CO: +57 1 288 3247<br>latam.medical@ansell.com | <b>Australia</b><br>Ansell Limited<br>T: +61 1800 337 041<br>F: +61 1800 803 578<br><br><b>Russia</b><br>Ansell PYC<br>Ten. +7 495 258 13 16 |
|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|----------------------------------------------------------------------------------------------------------------------------------------------|

Technology



Ansell, ® and ™ are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending: [www.ansell.com/patentmarking](http://www.ansell.com/patentmarking) © 2025 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.

