

# EDGE™

## 48-140 ESD

Light Duty Multi-purpose Industrial Glove



Multi Purpose



Medium Duty

## Multipurpose, light-duty work gloves, combining ESD compatibility, comfort and dexterity

- **Specialized protection:** EDGE™ 48-140 ESD protective gloves meet EN 16350:2014 and EN 1149-1/2/3 requirements for electrostatic dissipative materials, and can be used in explosion hazard (ATEX) zones as part of a grounding chain
- **Reduced electrostatic discharge risks:** EDGE™ 48-140 ESD safety work gloves feature anti-static capabilities and are designed to protect workers and electronic products and equipment from the potential dangers of static electricity
- **Elevated comfort:** These electronic discharge gloves are made of seamless 13-gauge polyester and carbon fiber liner that provide lightweight comfort and are the practical choice for final assembly tasks in the electrical and electronics industry.



### Industries

- Automotive
- Electronics

### Applications

- Final assembly of dashboard, cables and wires
- Final assembly of electronic components and mother boards

# EDGE™

## 48-140 ESD

Light Duty Multi-purpose Industrial Glove

### Key Features

- ◊ **ESD functionality:** Satisfies EN 16350:2014 European safety standard
- ◊ **Polyurethane coating:** For sweat-proof, anti-static industrial gloves
- ◊ **Seamless 13-gauge polyester:** Breathable comfort, optimized dexterity

### Performance Standards & Regulatory Compliance



EN 16350



EN388: 2016



3121A

### Specifications

| BRAND   STYLE    | DESCRIPTION                                                                                                                                        | Gauge | SIZE                  | LENGTH                         | COATING COLOR | PACKAGE                        |
|------------------|----------------------------------------------------------------------------------------------------------------------------------------------------|-------|-----------------------|--------------------------------|---------------|--------------------------------|
| EDGE™ 48-140 ESD | <b>Finishing:</b> Palm dipped<br><b>Coating Material:</b> Polyurethane<br><b>Liner Material:</b> Polyester, Carbon<br><b>Cuff Style:</b> Knitwrist | 13    | 5, 6, 7, 8, 9, 10, 11 | 220-270 mm / 8.66-10.63 inches | Grey          | • 12 pairs/bag, 12 bags/carton |

For additional information visit us at [www.ansell.com](http://www.ansell.com), or call us at

#### Europe, Middle East & Africa Region

Ansell Healthcare Europe NV  
Riverside Business Park  
Blvd International, 55  
1070 Brussels, Belgium  
T: +32 (0) 2 528 74 00  
F: +32 (0) 2 528 74 01

#### Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.  
Blvd. Bernardo Quintana No. 7001-C,  
Q7001 Torre II,  
Suites 1304, 1305 y 1306.  
Col. Centro Sur, c.p. 76079  
Queretaro, Qro. Mexico  
T: +52 442 248 1544 / 248 3133

#### North America Region

Ansell Healthcare Products LLC  
111 Wood Avenue South,  
Suite 900  
Iselin, NJ 08830, USA  
T: +1 800 800 0444  
F: +1 800 800 0445

#### Canada

Ansell Canada  
105 Lauder  
Cowansville, QC J2K 2K8  
Canada  
T: +1 800 363 8340  
F: +1 800 267 3551

#### Australia

Ansell Limited  
Level 3, 678 Victoria Street,  
Richmond, Vic, 3121  
Australia  
T: +61 1800 337 041  
F: +61 1800 803 578

#### Asia Pacific Region

Ansell Global Trading Center  
(Malaysia) Sdn Bhd  
Prima 6, Prima Avenue  
Block 3512, Jalan Teknokrat 6  
T: +603 8310 6688  
F: +603 8310 6699

Ansell, ® and ™ are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending: [www.ansell.com/patentmarking](http://www.ansell.com/patentmarking) © 2025 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.

**Ansell**