

Durable protection in a comfortable, versatile glove

- **Genuine versatility:** Designed for versatility, these nitrile gloves are ideal for a wide variety of industries in mid-duty applications
- **Secure grip:** Textured throughout the palm to ensure good grip in wet, dry and oily environments
- **Specialized protection:** The MICROFLEX™ 93-143 gloves have been tested for use with chemotherapy drugs*
- **Silicone-free:** These gloves are also silicone-free, allowing for better product protection



*see product packaging for details

Industries

- Automotive
- Life Sciences
- Food Processing

Recommended For

- Transferring liquids and solids
- Sample taking and processing
- Light assembly tasks
- Handling of paint/glue guns and sprayers
- Handling of tools
- Laboratory analysis
- Food processing and handling
- Assembly and inspection of components
- Chemical Handling
- Cleaning of plant and machines
- Blending, compounding materials
- Equipment repair and maintenance
- Maintenance

TECHNICAL DATA SHEET

	Product Information
Material	Nitrile
External Glove Surface	Fully Textured
Audit Standards	ISO 13485, ISO 9001
Product Certification	Medical Device Regulation (EU) 2017/745 Class I, Personal Protective Equipment Regulation (EU) 2016/425 Category III risks, ASTM D6319, EU Food Contact Approved, EC 2002/72, EC 2023/2006, EN ISO 21420:2020, EN ISO 374-1:2016 Type B KPT, EN ISO 374-5:2016 Virus, FDA21 CFR 177-2600-US Food Contact Approved, ISO 13485, ISO 18889:2019, ISO 9001
Packaging Overview	100 gloves per dispenser 10 dispensers per case 1000 gloves per case
Storage Instructions	Keep out of direct sunlight; store in a cool and dry place. Keep away from sources of ozone or ignition.
Country Of Origin	Malaysia
Product Segmentation	Multi-Purpose
Antistatic	Yes
Silicone Free	Yes

PHYSICAL PROPERTIES

	Typical Values		Testing Method
Length (mm/inches)	240 / 9.45		ASTM D3767,EN 420
Freedom from Holes (Inspection level I)	1.5 AQL		ASTM D5151,EN 374-2
Palm Thickness (mm/mils)	0.11 / 4.3		ASTM D3767,EN 420
Finger Thickness (mm/mils)	0.12 / 4.7		ASTM D3767,EN 420
	BEFORE AGING	AFTER AGING	
Elongation at Break (%)	500	400	ASTM D412
Force at break (N)	6	6	EN 455-2

ORDERING INFORMATION

Size	XS (5.5 - 6)	S (6.5 - 7)	M (7.5 - 8)	L (8.5 - 9)	XL (9.5 - 10)
Product Code	93143060	93143070	93143080	93143090	931430100

Performance Standards and Regulatory Compliance



For additional information visit us at www.ansell.com, or call us at

Europe, Middle East & Africa Region

Ansell Healthcare Europe NV

T: +32 (0) 2 528 74 00
F: +32 (0) 2 528 74 01

Asia Pacific Region

MY: +603 8310 6688
apac.medical@ansell.com
CN: +86 21 38275000
infochina@ansell.com
JP: +813 5549 8151
info.medical.jp@ansell.com

North America Region

Ansell Healthcare Products LLC
T: +1 800 800 0444
F: +1 800 800 0445

Latin America & Caribbean Region

BR: +55 (11) 3356-3100
latam.medical@ansell.com
MX: +52 442 296 2050
latam.medical@ansell.com
CO: +57 1 288 3247
latam.medical@ansell.com

Australia

Ansell Limited
T: +61 1800 337 041
F: +61 1800 803 578

Russia

Ansell PYC
Ten. +7 495 258 13 16

Ansell, ® and ™ are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending: www.ansell.com/patentmarking © 2025 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.

